



REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW DRAWING	27FEB2012	DMS	ST.P
	BA1	REVISED PER ECR-19-010572	11JUL2019	SR	AP



NOTE:

FOR FURTHER INFORMATION PLEASE SEE TLRS SERIES DATA SHEET

© 2019 TE Connectivity. All Rights Reserved.




DIMENSIONS:		DWN	27FEB2012	MATERIAL		FINISH	
mm		DARSHAN MS		-		-	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK	27FEB2012	TE Connectivity			
		ALLAN P					
		APVD	27FEB2012				
		STEPHEN.P					
0 PLC ±		PRODUCT SPEC		NAME CHIP SHUT RESISTOR TLRS 1050 SERIES			
1 PLC ±		-					
2 PLC ±		APPLICATION SPEC		SIZECAGE CODEDRAWING NORESTRICTED TO			
3 PLC ±		-					
4 PLC ±							
ANGLES ±°		WEIGHT					
CUSTOMER DRAWING				SCALE		SHEET	
				6:1		1 OF 2	
						REV	
						BA1	

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

TCPN	PRODUCT NUMBER	RESISTANCE (mΩ)	MATERIAL	H1 nom (mm)	H2 nom (mm)	WEIGHT (GR)
2176076-1	TLRS105040WR0005FTDG	0.5	MANGANIN	0.76	0.88	0.42
2176076-2	TLRS105040PR001FTDG	1	MANGANIN	0.38	0.43	0.22
2176076-3	TLRS105040ER002FTDG	2	NiCr ALLOY	0.69	0.64	0.31
2176076-4	TLRS105030ER003FTDG	3	NiCr ALLOY	0.43	0.43	0.21
2176076-5	TLRS105025ER004FTDG	4	NiCr ALLOY	0.32	0.32	0.16
2176076-6	TLRS105050WR0002FTDG	0.2	MANGANIN	1.42	1.42	0.74
2176076-7	TLRS105050WR0003FTDG	0.3	MANGANIN	1.42	1.42	0.7
2176076-8	TLRS105020ER005FTDG	5	NiCr ALLOY	0.35	0.25	0.11

© 2019 TE Connectivity. All Rights Reserved.

DIMENSIONS: mm		DWN DARSHAN MS 27FEB2012	MATERIAL -		FINISH -	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±°		CHK ALLAN P 27FEB2012	 TE Connectivity			
		APVD STEPHEN.P 27FEB2012				
		PRODUCT SPEC -	NAME CHIP SHUT RESISTOR TLRS 1050 SERIES			
		APPLICATION SPEC -				
		WEIGHT -	SIZE A 4	CAGE CODE 00779	DRAWING NO C-2176076	RESTRICTED TO -
		CUSTOMER DRAWING			SCALE 6:1	SHEET 2 OF 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2176076-1](#)