



REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW DRAWING	27FEB2012	DMS	ST.P
	BA1	REVISED PER ECR-19-010572	11JUL2019	SR	AP




NOTE:

FOR FURTHER INFORMATION PLEASE SEE TLRS SERIES DATA SHEET

© 2019 TE Connectivity. All Rights Reserved.




DIMENSIONS:		DWN	27FEB2012	MATERIAL	FINISH	
mm		DARSHAN MS				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK	27FEB2012	 TE Connectivity		
		ALLAN P				
		APVD	27FEB2012			
		STEPHEN.P				
0 PLC $\pm$		PRODUCT SPEC		NAME		
1 PLC $\pm$		-		CHIP SHUT RESISTOR		
2 PLC $\pm$		APPLICATION SPEC		TLRS 1050 SERIES		
3 PLC $\pm$		-		SIZE		
4 PLC $\pm$		WEIGHT		CAGE CODE		
ANGLES $\pm 1^\circ$		-		DRAWING NO		
		-		RESTRICTED TO		
CUSTOMER DRAWING		A 4		00779 C-2176076		
SCALE		6:1		SHEET 1 OF 2		
				REV BA1		

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

TCPN	PRODUCT NUMBER	RESISTANCE (mΩ)	MATERIAL	H1 nom (mm)	H2 nom (mm)	WEIGHT (GR)
2176076-1	TLRS105040WR0005FTDG	0.5	MANGANIN	0.76	0.88	0.42
2176076-2	TLRS105040PR001FTDG	1	MANGANIN	0.38	0.43	0.22
2176076-3	TLRS105040ER002FTDG	2	NiCr ALLOY	0.69	0.64	0.31
2176076-4	TLRS105030ER003FTDG	3	NiCr ALLOY	0.43	0.43	0.21
2176076-5	TLRS105025ER004FTDG	4	NiCr ALLOY	0.32	0.32	0.16
2176076-6	TLRS105050WR0002FTDG	0.2	MANGANIN	1.42	1.42	0.74
2176076-7	TLRS105050WR0003FTDG	0.3	MANGANIN	1.42	1.42	0.7
2176076-8	TLRS105020ER005FTDG	5	NiCr ALLOY	0.35	0.25	0.11

© 2019 TE Connectivity. All Rights Reserved.

DIMENSIONS: mm		DWN DARSHAN MS 27FEB2012		MATERIAL - FINISH -	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±°		CHK ALLAN P 27FEB2012		 TE Connectivity	
		APVD STEPHEN.P 27FEB2012			
		PRODUCT SPEC -		NAME CHIP SHUT RESISTOR TLRS 1050 SERIES	
		APPLICATION SPEC -			
		WEIGHT -		SIZE A 4 CAGE CODE 00779 DRAWING NO C-2176076 RESTRICTED TO -	
CUSTOMER DRAWING				SCALE 6:1 SHEET 2 OF 2 REV BA1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[TLRS105040WR0005FTDG](#)