





P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	06FEB2021	SR	AP



PTFE INSULATED CABLE



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SUPREETH R 06FEB2021	TE Connectivity		
DIMENSIONS: mm		CHK A. PILE 06FEB2021			
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD A. PILE 06FEB2021	NAME Aluminium Housed Breaking Resistor Type HCH265		
		PRODUCT SPEC	-		
MATERIAL	FINISH	APPLICATION SPEC	-		
		WEIGHT	-		
-	-	CUSTOMER DRAWING	SIZE A3	CAGE CODE 00779	DRAWING NO C-2176465
-	-		SCALE 1:2	SHEET 1 OF 2	RESTRICTED TO REV A

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-


SCHEDULE

TCPN	PRODUCT NUMBER	MATERIAL DESCRIPTION	LEAD LENGTH
2176465-1	HCH265J10RJ	HCH265 400W 10R 5% LEAD	300mm
2176465-2	HCH265J22RJ	HCH265 400W 22R 5% LEAD	300mm
2176465-3	HCH265J33RJ	HCH265 400W 33R 5% LEAD	300mm
2176465-4	HCH265J47RJ	HCH265 400W 47R 5% LEAD	300mm
2176465-5	HCH265J68RJ	HCH265 400W 68R 5% LEAD	300mm
2176465-6	HCH265J82RJ	HCH265 400W 82R 5% LEAD	300mm
2176465-7	HCH265J100RJ	HCH265 400W 100R 5% LEAD	300mm
2176465-8	HCH265J220RJ	HCH265 400W 220R 5% LEAD	300mm

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±

1 PLC ±

2 PLC ±

3 PLC ±

4 PLC ±

ANGLES ±

MATERIAL

-

-

DWN SUPREETH R 06FEB2021

CHK A. PILE 06FEB2021

APVD A. PILE 06FEB2021

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

SCALE 1:1

SHEET 2 OF 2

REV A

TE Connectivity

NAME

Aluminium Housed Breaking Resistor Type HCH265

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-2176465

-

1470-19 (3/13)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[HCH265J10RJ](#) [HCH265J82RJ](#) [HCH265J220RJ](#) [HCH265J68RJ](#) [HCH265J47RJ](#) [HCH265J22RJ](#) [HCH265J33RJ](#)
[HCH265J100RJ](#)