





| P | LTR | DESCRIPTION     | DATE      | DWN | APVD |
|---|-----|-----------------|-----------|-----|------|
|   | A   | INITIAL RELEASE | 06FEB2021 | SR  | AP   |
|   |     |                 |           |     |      |
|   |     |                 |           |     |      |



PTFE INSULATED CABLE




3:10  
ISO

THIS DRAWING IS A CONTROLLED DOCUMENT.

| DIMENSIONS: | TOLERANCES UNLESS OTHERWISE SPECIFIED: |
|-------------|----------------------------------------|
| mm          |                                        |
|             | 0 PLC ±0.1                             |
|             | 1 PLC ±0.1                             |
|             | 2 PLC ±0.1                             |
|             | 3 PLC ±0.1                             |
|             | 4 PLC ±0.1                             |
|             | ANGLES ±0.1                            |
| MATERIAL    | FINISH                                 |
| -           | -                                      |
| -           | -                                      |

|                  |            |           |
|------------------|------------|-----------|
| DWN              | SUPREETH R | 06FEB2021 |
| CHK              | A. PILE    | 06FEB2021 |
| APVD             | A. PILE    | 06FEB2021 |
| PRODUCT SPEC     | -          |           |
| APPLICATION SPEC | -          |           |
| WEIGHT           | -          |           |
| CUSTOMER DRAWING |            |           |



Aluminium Housed Breaking Resistor  
Type HCH335

| SIZE      | CAGE CODE | DRAWING NO   | RESTRICTED TO |
|-----------|-----------|--------------|---------------|
| A3        | 00779     | C-2176466    | -             |
| SCALE 1:2 |           | SHEET 1 OF 2 | REV A         |

REVISIONS

| P | LTR | DESCRIPTION | DATE | DWN | APVD |
|---|-----|-------------|------|-----|------|
|   | -   | SEE SHEET 1 | -    | -   | -    |
|   |     |             |      |     |      |
|   |     |             |      |     |      |
|   |     |             |      |     |      |


SCHEDULE

| TCPN      | PRODUCT NUMBER | MATERIAL DESCRIPTION     | LEAD LENGTH |
|-----------|----------------|--------------------------|-------------|
| 2176466-1 | HCH335J10RJ    | HCH335 500W 10R 5% LEAD  | 300mm       |
| 2176466-2 | HCH335J22RJ    | HCH335 500W 22R 5% LEAD  | 300mm       |
| 2176466-3 | HCH335J33RJ    | HCH335 500W 33R 5% LEAD  | 300mm       |
| 2176466-4 | HCH335J47RJ    | HCH335 500W 47R 5% LEAD  | 300mm       |
| 2176466-5 | HCH335J68RJ    | HCH335 500W 68R 5% LEAD  | 300mm       |
| 2176466-6 | HCH335J82RJ    | HCH335 500W 82R 5% LEAD  | 300mm       |
| 2176466-7 | HCH335J100RJ   | HCH335 500W 100R 5% LEAD | 300mm       |
| 2176466-8 | HCH335J220RJ   | HCH335 500W 220R 5% LEAD | 300mm       |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±  
1 PLC ±  
2 PLC ±  
3 PLC ±  
4 PLC ±  
ANGLES ±  
FINISH -

MATERIAL

-

DWN SUPREETH R 06FEB2021

CHK A. PILE 06FEB2021

APVD A. PILE 06FEB2021

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

NAME

Aluminium Housed Breaking Resistor  
Type HCH335

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-2176466

-

SCALE

1:1

SHEET

2 OF 2

REV

A

1470-19 (3/13)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2176466-3](#) [2176466-7](#) [2176466-2](#) [2176466-5](#) [2176466-1](#) [2176466-8](#) [2176466-6](#) [2176466-4](#)