







NOTES
Bemerkungen

1 SUPPLIED FROM: LOOSE PIECE PACKED INTO CARTON
Lieferform: Schuettgut in Karton verpackt



0-2177526-4	16.2±0.25	ANTI ROTATION SAFEGUARD -HV-1POS.-IPT 50 mm ² Verdrehschutz-HV-1pol. -IPT 50 mm ²	PA66-GF30	ORANGE SIMILAR TO RAL 2003 Aehnlich RAL2003	1.3
0-2177526-3	15.3±0.25	ANTI ROTATION SAFEGUARD -HV-1POS.-IPT 35 mm ² Verdrehschutz-HV-1pol. -IPT 35 mm ²	PA66-GF30	ORANGE SIMILAR TO RAL 2003 Aehnlich RAL2003	1.5
0-2177526-2	13.1±0.25	ANTI ROTATION SAFEGUARD -HV-1POS.-IPT 25 mm ² Verdrehschutz-HV-1pol. -IPT 25 mm ²	PA66-GF30	ORANGE SIMILAR TO RAL 2003 Aehnlich RAL2003	1.8
0-2177526-1	11.2±0.25	ANTI ROTATION SAFEGUARD -HV-1POS.-IPT 16 mm ² Verdrehschutz-HV-1pol. -IPT 16 mm ²	PA66-GF30	ORANGE SIMILAR TO RAL 2003 Aehnlich RAL2003	1.95
TE PN	DIMENSION A	DESCRIPTION	MATERIAL	COLOR	VOLUME [cm ³]

		TOLERANCING ISO 8015 TOLERIERUNG ISO 8015						
DIESE ZEICHNUNG IST EIN KONTROLLIERTES DOKUMENT. BEMASSUNGEN UND TOLERANZEN GEMAESS GPS (ISO STANDARDS).								
THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER GPS (ISO STANDARDS).		DWN Maithreya K.P. 25APR2013 CHK Vishwa.A 25APR2013 APVD F. Kaehny 25APR2013	 TE Connectivity NAME ANTI ROTATION SAFEGUARD HV-1-POS.-IPT Verdreherschutz-HV-1 pol.-IPT					
DIMENSIONS: MASSEINHEITEN: (mm)	TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN	PRODUCT SPEC PRODUKTSPEZ. -						
	0 PLC ± DIN ISO 2768-m-H 1 PLC ± DIN 16901-130 2 PLC ± 3 PLC ± 4 PLC ± ANGLES/WINKEL ±°	APPLICATION SPEC VERARBEITUNGSSPEZ. -						
MATERIAL SEE TABLE	FINISH/OBERFLAECHE/FARBE -	WEIGHT GEWICHT -						
		SIZE A3	CAGE CODE 00779	DRAWING NO ZEICHNUNGS-NR. C=2177526	RESTRICTED TO NUR FUEUR -			
		Customer Drawing		/KUNDENZEICHNUNG	SCALE MASSSTAB 2:1	SHEET BLATT 1	OF VON 1	REV B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2177526-2](#)