







THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT -



ALL RIGHTS RESERVED.

REFERENCE MATING INTERFACE PATTERN:
1,27 STAGGERED PITCH x 1,5 ROW-DISTANCE.



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A		INITIAL RELEASE	08AUG2014	PS	JK

1 PARTNUMBER VAC. TAPE.	3 PARTNUMBER	NO.OF POS. "n"	"A"	"B" MAX.
7-2178711-4	2178711-4	4	3,81	7,1
7-2178711-6	2178711-6	6	6,35	9,7
7-2178711-8	2178711-8	8	8,89	12,2
8-2178711-0	1-2178711-0	10	11,43	14,7
8-2178711-2	1-2178711-2	12	13,97	17,3
8-2178711-4	1-2178711-4	14	16,51	19,8
8-2178711-6	1-2178711-6	16	19,05	22,4
8-2178711-8	1-2178711-8	18	21,59	24,9
9-2178711-0	2-2178711-0	20	24,13	27,5



NOTES:

- 1 TAPE FOR VACUUM P&P ONLY FOR DASHNUMBERS 7- /8- /9-
- 2 FOR PACKAGING SEE SHEET 2 OF 2
- 3 WITHOUT VACUUM TAPE.
- 4 CORING-OUTS FOR MANUFACTURING PURPOSE ONLY. SHAPE MAY VARY, BUT IS NOT FUNCTIONAL FOR THE APPLICATION.
- 5 SHOWN IS A 10 POSITION CONNECTOR.

3	PICK & PLACE TAPE	KAPTON	AMBER TRANSPARENT
2	FEMALE HOUSING	POLYAMIDE 4/6,GF	BLACK
1	FEMALE CONTACT	TIN BRASS	3.0 - 5.0µm TIN OVER 0.5µm NICKEL
ITEM NO.	COMPONENT DESCRIPTION	MATERIAL	FINISH / COLOR

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN PRASHANTH 30JUL2014		
DIMENSIONS: mm		CHK PRASHANTH 05AUG2014		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD JAYANTH KUMAR 05AUG2014	NAME Micro-MaTch VALUE LINE FEMALE-ON-BOARD, TOP ENTRY, SMD, CONNECTOR	
0 PLC ±-		PRODUCT SPEC 108-32087		
1 PLC ±-		APPLICATION SPEC 114-13318	SIZE A3 CAGE CODE 00779 DRAWING NO C-2178711	
2 PLC ±-		WEIGHT -		
3 PLC ±-		CUSTOMER DRAWING	RESTRICTED TO -	
4 PLC ±-		SCALE 5:1		
5 PLC ±-		SHEET 1 OF 2	REV A	
ANGLES ±-				
FINISH SEE TABLE				

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD





SEE SHEET 1

TAPE WIDTH
24 mm

TAPE WIDTH
24 mm

TAPE WIDTH
24 mm

TAPE WIDTH
24 mm







7-2178711-4
4 POSITION
2178711-4

7-2178711-6
6 POSITION
2178711-6

7-2178711-8
8 POSITION
2178711-8

8-2178711-0
10 POSITION
1-2178711-0








TAPE WIDTH 44 mm

TAPE WIDTH 44 mm

TAPE WIDTH 44 mm

TAPE WIDTH 44 mm

TAPE WIDTH 44 mm








8-2178711-2
12 POSITION
1-2178711-2

8-2178711-4
14 POSITION
1-2178711-4

8-2178711-6
16 POSITION
1-2178711-6

8-2178711-8
18 POSITION
1-2178711-8


9-2178711-0
20 POSITION
2-2178711-0



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±0.1
2 PLC ±0.05
3 PLC ±
4 PLC ±
ANGLES ±
FINISH

MATERIAL

-

DWN 25JUL2014
PRASHANTH

CHK 05AUG2014
PRASHANTH

APVD 05AUG2014
JAYANTH KUMAR

PRODUCT SPEC

108-32087

APPLICATION SPEC

114-13318

WEIGHT

-

CUSTOMER DRAWING



TE Connectivity

NAME
Micro-MaTch VALUE LINE
FEMALE-ON-BOARD, TOP ENTRY,
SMD, CONNECTOR

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-2178711

-

SCALE

1:1

SHEET

2

OF

2

REV

A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[7-2178711-4](#)