





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D1	REV PER ECO 17-011144	8-16-17	CT	DM



.426 [10.82]	.039 [0.99]	.596 [15.14]	.668 [16.97]	2.302 [58.47]	.230 [5.84]	2.729 [69.32]	2.500 [63.50]	.503 [12.78]	2.212 [56.18]	104	1-2221860-6
.426 [10.82]	.039 [0.99]	.534 [13.56]	.605 [15.37]	2.178 [55.32]	.230 [5.84]	2.635 [66.93]	2.406 [61.11]	.441 [11.20]	2.079 [52.81]	78	1-2221860-5
.426 [10.82]	.039 [0.99]	.422 [10.72]	.494 [12.55]	2.272 [57.71]	.230 [5.84]	2.729 [69.32]	2.500 [63.50]	.329 [8.36]	2.182 [55.42]	62	1-2221860-4
.426 [10.82]	.039 [0.99]	.422 [10.72]	.494 [12.55]	1.625 [41.27]	.230 [5.84]	2.088 [53.03]	1.852 [47.04]	.329 [8.36]	1.534 [39.96]	44	1-2221860-3
.422 [10.72]	.030 [0.76]	.422 [10.72]	.494 [12.55]	1.083 [27.51]	.235 [5.97]	1.541 [39.14]	1.312 [33.32]	.329 [8.36]	.994 [25.25]	26	1-2221860-2
.422 [10.72]	.030 [0.76]	.422 [10.72]	.494 [12.55]	.759 [19.28]	.235 [5.97]	1.213 [30.81]	.984 [24.99]	.329 [8.36]	.666 [16.92]	15	1-2221860-1
.426 [10.82]	.039 [0.99]	.596 [15.14]	.668 [16.97]	2.302 [58.47]	.230 [5.84]	2.729 [69.32]	2.500 [63.50]	.503 [12.78]	2.212 [56.18]	104	2221860-6
.426 [10.82]	.039 [0.99]	.534 [13.56]	.605 [15.37]	2.178 [55.32]	.230 [5.84]	2.635 [66.93]	2.406 [61.11]	.441 [11.20]	2.079 [52.81]	78	2221860-5
.426 [10.82]	.039 [0.99]	.422 [10.72]	.494 [12.55]	2.272 [57.71]	.230 [5.84]	2.729 [69.32]	2.500 [63.50]	.329 [8.36]	2.182 [55.42]	62	2221860-4
.426 [10.82]	.039 [0.99]	.422 [10.72]	.494 [12.55]	1.625 [41.27]	.230 [5.84]	2.088 [53.03]	1.852 [47.04]	.329 [8.36]	1.534 [39.96]	44	2221860-3
.422 [10.72]	.030 [0.76]	.422 [10.72]	.494 [12.55]	1.083 [27.51]	.235 [5.97]	1.541 [39.14]	1.312 [33.32]	.329 [8.36]	.994 [25.25]	26	2221860-2
.422 [10.72]	.030 [0.76]	.422 [10.72]	.494 [12.55]	.759 [19.28]	.235 [5.97]	1.213 [30.81]	.984 [24.99]	.329 [8.36]	.666 [16.92]	15	2221860-1
DIM L	DIM K	DIM J	DIM H	DIM G	DIM F	DIM D	DIM C	DIM B	DIM A	NO. OF POSITIONS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 10-14-14 C.C.THOMAS CHK 10-14-14 C.DERRICK		 TE Connectivity	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± .- 1 PLC ± .- 2 PLC ± .- 3 PLC ± .005 [0.13] 4 PLC ± .- 4 ANGLES ± .1"		NAME PLUG ASSY, SIZE 1-6, IP67 SERIES 90, AMPLITUDE WITH IF SEAL AND GROMMET	
		APVD 10-14-14 C.DERRICK PRODUCT SPEC APPLICATION SPEC		SIZE A1	
MATERIAL SEE CALLOUTS		WEIGHT 0.000000		CAGE CODE 00779	
FINISH SEE CALLOUTS		CUSTOMER DRAWING		DRAWING NO 2221860	
				SCALE 4:1 SHEET 1 of 1 REV D	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2221860-2](#)