






1. TEMPERATURE RANGE: -55°C TO +175°C
2. MATERIAL: THERMOPLASTIC, FLUOROSILICONE
3. CHARACTERISTICS:
 - DELIVERED WITHOUT CONTACTS, MUST BE ORDERED SEPARATELY
 - PIN #16 CONTACTS (QTY=6) PER MIL-C 39029/58-364 (DEUTSCH P/N 38941-16L)
 - PIN #22 CONTACTS (QTY=2) PER MIL-C 39029/58-360 (DEUTSCH P/N 38941-22L)
 - PIN GbE CONTACTS (QTY=8) (DEUTSCH P/N 605705-31 OR 724-0001-24 OR TE P/N 2226891-1)
4. HAND CRIMP TOOL FOR GbE CONTACTS:
 - DMC M22520/2-01, SETTING NUMBER 3
 - POSITIONER: K1587
5. COMPATIBLE WITH ARINC 809 PLUG SHELLS (DEUTSCH P/N DMC-MD20 SERIES)
6. COMPATIBLE WITH ARINC 809 RECEPTACLE SHELLS (DEUTSCH P/N DMC-MD24 AND DMC-MD26 SERIES)



SCALE 4:1



2226454-1
ASSEMBLY, PIN, INSERT MODULE

2226454-1
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DLB 29MAY2013	TE Connectivity	
		CHK R LUENTE 29MAY2013		
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME
mm		0 PLC ±.5		ASSEMBLY, PIN, INSERT MODULE
		1 PLC ±.5		CABLE ATTACH, GbE + POWER
		2 PLC ±.13		
		3 PLC ±.013		
		4 PLC ±.0001		
		ANGLES		
		FINISH		
MATERIAL		WEIGHT	SIZE	CAGE CODE
-		-	A	00779
-		-	C	2226454
		CUSTOMER DRAWING	SCALE	8:1
			SHEET	1
			OF	1
			REV	H

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2226454-1](#)