

LOC		DIST		REVISIONS					
GP		00		P	LTR	DESCRIPTION	DATE	DWN	APVD
					A	REVISED PER ECO-15-000199	13JAN2015	AP	DG
					C	REVISED PER ECO-18-008478	10MAY2018	JY	SH

- 1 MATERIALS
HOUSINGS AND CHICKLETS: LCP, BLACK, UL94V-O RATED
CONTACTS: COPPER ALLOY
- 2 CONTACT FINISH: CONFORMS TO THE REQUIREMENTS OF TE PRODUCT SPECIFICATION, 108-32038. BASED ON EIA/ECA-364-1000.01A. (CONTROLLED ENVIRONMENT APPLICATIONS) ON MATING END. TIN PLATED ON PCB TAIL





3. MATES WITH TE PLUG 2227603-1

- 4 MOUNTING HARDWARE M2x1.35 SELF-THREADING SCREW
SCREW LENGTH OF FASTENER = PCB THICKNESS + 3.0mm MAX (1.75mm MIN)
MOUNTING HARDWARE IS NOT SUPPLIED BY TE.

- 5 RECOMMENDED COMPONENT KEEP OUT ZONE.

- 6 PART NUMBER AND DATE CODE MARKED IN APPROXIMATE AREA SHOWN ON OPPOSITE SIDE.

- 7 MOUNTING HARDWARE M2x0.0.78 OR M1.8x0.709 SELF-THREADING SCREW (DELTA PT® THREAD-FORMING FASTENER), SCREW LENGTH OF FASTENER = PCB THICKNESS + 5.0mm MAX (1.75mm MIN),
MOUNTING HARDWARE IS NOT SUPPLIED BY TE.




SCALE 4:1


7	Ø1.60	2227582-2
4	Ø1.80	2227582-1
SCREW APPLICATION	DIAMETER OF SCREW HOLES	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. TREA CHK R. HENRY APVD	20DEC2012	NAME	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	
mm		0 PLC ±		108-32038	
		1 PLC ±0.13		APPLICATION SPEC	
		2 PLC ±		114-32101	
		3 PLC ±		WEIGHT	
		4 PLC ±		CUSTOMER DRAWING	
		ANGLES		SIZE	
		FINISH		CAGE CODE DRAWING NO	
MATERIAL		:		A100779C=2227582	
				RESTRICTED TO	
				SCALE 6:1 SHEET 1 OF 3 REV C	

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00	-	-	SEE SHEET 1	-	-	-



2227582-1
SCALE 6:1



2227582-2
SCALE 6:1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
R. TREA

CHK
R. HENRY

APVD

20DEC2012

DIMENSIONS:

mm

0 PLC ±"

1 PLC ±"

2 PLC ±0.13

3 PLC ±"

4 PLC ±"

ANGLES ±"

FINISH -

TOLERANCES UNLESS OTHERWISE SPECIFIED:

PRODUCT SPEC

108-32038

APPLICATION SPEC

114-32101

WEIGHT -

CUSTOMER DRAWING

NAME

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

TE Connectivity

RECEPTACLE ASSEMBLY,
1X4, RIGHT ANGLE,
INTERNAL MINI-SAS HD

A100779



C=2227582

SCALE 6:1



SHEET 2 OF 3

REV C

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00	-	-	SEE SHEET 1	-	-	-



DETAIL A
SCALE 20:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. TREA	20DEC2012	 TE Connectivity	
		CHK R. HENRY	20DEC2012		
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
mm		0 PLC ±		PRODUCT SPEC	
		1 PLC ±		108-32038	
		2 PLC ± .0013		APPLICATION SPEC	
		3 PLC ±		114-32101	
		4 PLC ±		WEIGHT	
MATERIAL		FINISH		SIZE CAGE CODE DRAWING NO	
-		-		A100779C=2227582	
CUSTOMER DRAWING				RESTRICTED TO	
				SCALE 6:1	SHEET 3 OF 3 REV C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2227582-1](#)