




TAPING STYLE B: 5,7POS



TAPING STYLE B: 4,6,8POS




TAPING STYLE A: 2,3POS




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A1		ECR-16-017015	10EC2016	A.O	D.2
A2		ECR-18-016738	23OCT2018	C.X	D.2

NOTE:
1. ACCUMULATING TOLERANCE : ≤1.0mm/20 PITCH
△ MEASURING POINT : AT TOP OF POST
△ TAPE MUST NOT PROTRUDE FROM BACKING PAPER
△ MEASURING POINT, THE TOP OF TAPING AND THE CENTER LINE OF LEAD WIRE 1IN BETWEEN
△ BE BASED ON THE CENTER 12.7mm PITCH DIMENSION
△ DIMENSIONS ARE FOR ALL POSITION.
△ APPLICABLE P.C.B. HOLE DIA: ØA1.1±0.1mm
△ PRELIMINARY-NOT FOR PRODUCTION

FIGURE OF PILING ROW



PCB MOUTING LAYOUT



KEYING

D	BLACK	5
D	YELLOW	4
C	RED	3
B	BLUE	2
A	NATURAL	1
KEYING	COLOR	X

ITEM	NAME	MATERIAL
①	HEAD HOUSING	66 NYLON GF UL94V-0
②	LONG POST CONTACT	BRASS;
③	SHORT POST CONTACT	FINISH: Tin OVER Ni
④	RADIAL TAPE	THERMAL PAPER
⑤	BACKING PAPER	CRAFT PAPER

*	*	/	*	*	/	*	*	450	B	17.5	8	22.5	8	8-2232542-X	8-2232546-X	△
	*	*	/	*	/	*	*	450	C	15	7	20.0	7	7-2232542-X	7-2232546-X	△
		*	/	*	*	/	*	450	B	12.5	6	17.5	6	6-2232542-X	6-2232546-X	
			*	/	*	/	*	450	C	10	5	15.0	5	5-2232542-X	5-2232546-X	
				/	*	*	/	450	B	7.5	4	12.5	4	4-2232542-X	4-2232546-X	
					/	*	/	900	A	5	3	10.0	3	3-2232542-X	3-2232546-X	
						/	/	900	A	2.5	2	7.5	2	2-2232542-X	2-2232546-X	
8	7	6	5	4	3	2	1	QTY	TAPING STYLE	M	N	E	POS	HEAD ASS 1	STRIP ASS	
CIRCUIT NO.												X=1.2.3.4.5				

/: LONG PIN 2232707-4
*:SHORT PIN 2232707-3

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN	ANNIE QIAN	18-JAN-16	TE Connectivity			
DIMENSIONS:				CHK	DANIEL ZHANG	18-JAN-16				
mm				APVD	DANIEL ZHANG	18-JAN-16	NAME			
				PRODUCT SPEC			GRACE INERTIA 2.5 CONNECTOR			
				APPLICATION SPEC			HEADER ON TAPE			
MATERIAL				WEIGHT			SIZE			
							A1			
							CAGE CODE			
							C=2232546			
							DRAWING NO			
							SHEET			
							1 OF 1			
							REV			
							A2			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3-2232546-5](#)