



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AJ	16		N1	REVISED PER ECO-11-005030	11MAR11	RK	HMR



1. ACCEPTS COAX CABLE WITH .095-.110 O.D. JACKETS AND .055-.065 DIELECTRIC O.D.
EXAMPLE: RG-174 AND RG-316

2. TIN PLATE PER ASTM-B-545.

3. INSTRUCTION SHEET NO.: 408-2472-2.





4. ON STRIP

5. ON STRIP, LEGS MUST BE BENT MANUALLY AFTER CRIMPING.

6. LOOSE PIECE PARTS WITH PREFORMED LEGS.

7. BRASS PER ASTM-B-36.

8. TIN-LEAD PLATE PER ASTM-B-545.




VIEW C



VIEW D

SECTION A-A

SECTION B-B



PCB LAYOUT




AS APPLIED BY APPLICATOR

AS APPLIED BY APPLICATOR

VIEW E

VIEW F

2	D	6	9-226176-2
2	C&F	5	9-226176-1
2	C&E	4	9-226176-0
8	D	6	226176-4
8	C&F	5	226176-3
8	C&E	4	226176-2
FINISH	VIEW	TYPE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. OBRINE 30JUN99	 TE Connectivity					
		CHK M. OBRINE 30JUN99						
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD J. CABRILLO 30JUN99	NAME BRAID-PIC P.C. BOARD GROUND TERMINAL SINGLE CRIMP-SINGLE CONTACT					
	0 PLC ± -	PRODUCT SPEC						
	1 PLC ± -	—						
	2 PLC ± -	APPLICATION SPEC						
	3 PLC ± .008	—						
	4 PLC ± -	—						
ANGLES ± -	—	SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO		
MATERIAL	FINISH	WEIGHT .007 OZ	A2	00779	C-226176		—	
SEE NOTE 7	SEE TABLE	CUSTOMER DRAWING				SCALE 6:1	SHEET 1 of 1	REV N1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[226176-3](#)