

1

MATERIAL:

CONNECTOR HOUSING: UL94 V-0 RATED THERMOPLASTIC, COLOR: WHITE

LATCH: THERMOPLASTIC, COLOR: BLACK

CABLE JACKET: THERMOPLASTIC ELASTOMER, COLOR: BLACK

CABLE CONDUCTORS: COPPER ALLOY

CONNECTOR CONTACTS: BRASS ALLOY

2

FINISH:

CONNECTOR CONTACTS: SILVER OVER NICKEL


3

CHARGING CABLE: TE CONNECTIVITY PROPRIETARY

UL LISTING: TYPE EVE

CABLE COLOR, LENGTH AND WIRE TERMINATIONS ARE FULLY CUSTOMIZABLE

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED PER ECO-15-013901	21SEP2015	RLK	MM
	B	REVISED PER ECO-16-007344	08JUN2016	RLK	MM
	C	REVISED PER ECO-17-003145	11MAR2017	RLK	MM



3	7.62m (25 FT)	2267185-4
	6.1m (20 FT)	2267185-3
	4.6m (15 FT)	2267185-2
	3.05m (10 FT)	2267185-1
CABLE	CABLE LENGTH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

RL KOLLER

21OCT2014

CHK

M. MERCURIO

23APR2015

APVD

G. DEFIBAUGH

25SEP2015

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±

1 PLC ±0.4

2 PLC ±

3 PLC ±

4 PLC ±

ANGLES ±2°

FINISH

MATERIAL

-

1

PRODUCT SPEC

108-32100

APPLICATION SPEC

-

WEIGHT

-

Customer Drawing

TE Connectivity

EV CONNECTOR ASSEMBLY

16mm CABLE, UL, WHITE

SIZE

A2

CAGE CODE

00779

DRAWING NO

C-2267185

RESTRICTED TO

-

SCALE

1:1

SHEET

1

OF

1

REV

C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2267185-1](#)