



4		3		2		1													
THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		LOC		DIST		REVISIONS											
© COPYRIGHT – By –		ALL RIGHTS RESERVED.		H		—		P		LTR		DESCRIPTION		DATE		DWN		APVD	
NOTES: Tolerances cable lengths: 0m to 0.5m +30mm 0.5m to 1.0m +50mm 1.0m to 3.0m +100mm < 3.0m +1.5%										A		INITIAL RELEASE		12NOV2013		GSK		BvH	
										A1		ECR-14-011671		14AUG2014		GSK		BvH	
TECHNICAL DATA																			
Operating voltage max. 60 V AC/DC																			
Operating current per contact max. 4 A																			
Locking of ports Screw thread M8 x 1 mm (recommended torque 0.4 Nm) self-securing																			
Protection IP65 and IP67 when plugged and screwed down (EN 60529)																			
PUR CABLE																			
No./diameter of wires 3 x 0.34 mm²																			
Wire isolation PP (br, bl, bk)																			
C-track properties 5 million																			
Jacket PUR (UL/CSA)																			
Outer diameter approx. 5.0 mm																			
Bend radius (moving) 10 x outer diameter																			
Temperature range (fixed) -40...+80 °C																			
Temperature range (mobile) -25...+80 °C																			
PVC CABLE																			
No./diameter of wires 3 X 0.34 mm²																			
Wire isolation PVC (br, bl, bk)																			
C-track properties																			
Jacket PVC (UL/CSA)																			
Outer diameter approx. 5.0 mm																			
Bend radius (moving) 10 x outer diameter																			
Temperature range (fixed) -30...+80 °C																			
Temperature range (mobile) -5...+80 °C																			
Contact Layout Female																			
																			
Schematic diagram																			
																			
3 pos																			
10mtr																			
5mtr																			
3mtr																			
1.5mtr																			
PVC																			
Black																			
1-2273005-4																			
3x22AWG PVC 10.0m																			
8																			
1-2273005-3																			
3x22AWG PVC 5.0m																			
7																			
1-2273005-2																			
3x22AWG PVC 3.0m																			
6																			
1-2273005-1																			
3x22AWG PVC 1.5m																			
5																			
3 pos																			
10mtr																			
5mtr																			
3mtr																			
1.5mtr																			
PUR																			
Black																			
2273005-4																			
3x22AWG PUR 10.0m																			
4																			
2273005-3																			
3x22AWG PUR 5.0m																			
3																			
2273005-2																			
3x22AWG PUR 3.0m																			
2																			
2273005-1																			
3x22AWG PUR 1.5m																			
1																			
LENGTH "L"																			
MATERIAL																			
JACKET COLOR																			
TE PN																			
DESCRIPTION																			
ITEM																			
THIS DRAWING IS A CONTROLLED DOCUMENT.																			
DWN 12NOV2013																			
SATHISH KUMAR .G																			
CHK 12NOV2013																			
B.VELDHOVEN																			
APVD 12NOV2013																			
A.VAN ZANDVOORT																			
PRODUCT SPEC																			
108-19483																			
APPLICATION SPEC																			
114-32127																			
WEIGHT																			
-																			
CUSTOMER DRAWING																			
SCALE																			
NTS																			
SHEET																			
1 OF 1																			
REV																			
A1																			
THIS DRAWING IS UNPUBLISHED.																			
RELEASED FOR PUBLICATION																			
LOC																			
DIST																			
REVISIONS																			
P																			
LTR																			
DESCRIPTION																			
DATE																			
DWN																			
APVD																			
A																			
INITIAL RELEASE																			
12NOV2013																			
GSK																			
BvH																			
A1																			
ECR-14-011671																			
14AUG2014																			
GSK																			
BvH																			
TECHNICAL DATA																			
Operating voltage max. 60 V AC/DC																			
Operating current per contact max. 4 A																			
Locking of ports Screw thread M8 x 1 mm (recommended torque 0.4 Nm) self-securing																			
Protection IP65 and IP67 when plugged and screwed down (EN 60529)																			
PUR CABLE																			
No./diameter of wires 3 x 0.34 mm²																			
Wire isolation PP (br, bl, bk)																			
C-track properties 5 million																			
Jacket PUR (UL/CSA)																			
Outer diameter approx. 5.0 mm																			
Bend radius (moving) 10 x outer diameter																			
Temperature range (fixed) -40...+80 °C																			
Temperature range (mobile) -25...+80 °C																			
PVC CABLE																			
No./diameter of wires 3 X 0.34 mm²																			
Wire isolation PVC (br, bl, bk)																			
C-track properties																			
Jacket PVC (UL/CSA)																			
Outer diameter approx. 5.0 mm																			
Bend radius (moving) 10 x outer diameter																			
Temperature range (fixed) -30...+80 °C																			
Temperature range (mobile) -5...+80 °C																			
Contact Layout Female																			
Schematic diagram																			
3 pos																			
10mtr																			
5mtr																			
3mtr																			
1.5mtr																			
PVC																			
Black																			
1-2273005-4																			
3x22AWG PVC 10.0m																			
8																			
1-2273005-3																			
3x22AWG PVC 5.0m																			
7																			
1-2273005-2																			
3x22AWG PVC 3.0m																			
6																			
1-2273005-1																			
3x22AWG PVC 1.5m																			
5																			
3 pos																			
10mtr																			
5mtr																			
3mtr																			
1.5mtr																			
PUR																			
Black																			
2273005-4																			
3x22AWG PUR 10.0m																			
4																			
2273005-3																			
3x22AWG PUR 5.0m																			
3																			
2273005-2																			
3x22AWG PUR 3.0m																			
2																			
2273005-1																			
3x22AWG PUR 1.5m																			
1																			
LENGTH "L"																			
MATERIAL																			
JACKET COLOR																			
TE PN																			
DESCRIPTION																			
ITEM																			
THIS DRAWING IS A CONTROLLED DOCUMENT.																			
DWN 12NOV2013																			
SATHISH KUMAR .G																			
CHK 12NOV2013																			
B.VELDHOVEN																			
APVD 12NOV2013																			
A.VAN ZANDVOORT																			
PRODUCT SPEC																			
108-19483																			
APPLICATION SPEC																			
114-32127																			
WEIGHT																			
-																			
CUSTOMER DRAWING																			
SCALE																			
NTS																			
SHEET																			
1 OF 1																			
REV																			
A1																			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2273005-4](#)