

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT – By – ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	12NOV2013	GSK	BvH
	A1	ECR–15–003371	04MAR2015	GSK	BvH

NOTES:

Tolerances cable lengths:

0m to 0.5m +30mm

0.5m to 1.0m +50mm

1.0m to 3.0m +100mm

< 3.0m +1.5%

A

L

VIEW 'A'

TECHNICAL DATA

Operating voltage	max. 30 V AC/DC
Operating current per contact	max. 4 A
Locking of ports	Screw thread M8 x 1 mm (recommended torque 0.4 Nm) self–securing
Protection	IP65 and IP67 when plugged and screwed down (EN 60529)
Temperature range	–25...+85 °C

CABLE

No./diameter of wires	3 x 0.25 mm²
Wire isolation	PP (br, bk, bl) (UL/CSA)
Outer diameter	approx. 2.7 mm
Bend radius (moving)	10 x outer diameter
Temperature range (fixed)	–40...+80 °C

3 pos	0.2mtr	2273013–1	3X22AWG PANELMOUNT 0.2m WIRES	1
	LENGTH”L”	TE PN	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

0 PLC ± –

1 PLC ± –

2 PLC ± –

3 PLC ± –

4 PLC ± –

ANGLES ± –

MATERIAL

–

TOLERANCES UNLESS OTHERWISE SPECIFIED:

± –

FINISH

–

DWN 12NOV2013

SATHISH KUMAR .G

CHK 12NOV2013

B.VELDHOVEN

APVD 12NOV2013

A.VAN ZANDVOORT

PRODUCT SPEC

108–19483

APPLICATION SPEC

114–32127

WEIGHT

–

CUSTOMER DRAWING

TE Connectivity

M8 FEMALE PANEL MLD REAR MT M8 3POS

–

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779

C=2273013

–

SCALE

NTS

SHEET

1 OF 1

REV

A1

1470–19 (3/11)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2273013-1](#)