



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	ECR-14-011671	16AUG2014	GSK	BvH
	A2	ECR-16-003945	16MAR2016	GSK	BvH
	A3	ECR-21-000466	07FEB2021	BP	CW

NOTES:
 Tolerances cable lengths:
 0m to 0.5m +30mm
 0.5m to 1.0m +50mm
 1.0m to 3.0m +100mm
 < 3.0m +1.5%



TECHNICAL DATA	
Operating voltage	max. 250 V AC/DC
Operating current per contact	max. 4 A
Locking of ports	Screw thread M12 x 1 mm (recommended torque 0.6 Nm) self-securing
Protection	IP65 and IP67 when plugged and screwed down (EN 60529)



PUR CABLE	
No./diameter of wires	3 x 0.34 mm ²
Wire isolation	PP (br, bl, bk)
C-track properties	5 million
Jacket	PUR (UL/CSA)
Outer diameter	approx. 4.3 mm
Bend radius (moving)	10 x outer diameter
Temperature range (fixed)	-40...+80 °C
Temperature range (mobile)	-25...+80 °C

LENGTH "L"	MATERIAL	JACKET COLOR	TE PN	DESCRIPTION	ITEM
3 pos	PVC	Black	1-2273023-4	3x22AWG PVC 10.0m	8
			1-2273023-3	3x22AWG PVC 5.0m	7
			1-2273023-2	3x22AWG PVC 3.0m	6
			1-2273023-1	3x22AWG PVC 1.5m	5
3 pos	PUR	Black	2273023-4	3x22AWG PUR 10.0m	4
			2273023-3	3x22AWG PUR 5.0m	3
			2273023-2	3x22AWG PUR 3.0m	2
			2273023-1	3x22AWG PUR 1.5m	1

PVC CABLE	
No./diameter of wires	3 x 0.34 mm ²
Wire isolation	PVC (br, bl, bk)
C-track properties	
Jacket	PVC (UL/CSA)
Outer diameter	approx. 4.6 mm
Bend radius (moving)	10 x outer diameter
Temperature range (fixed)	-30...+80 °C
Temperature range (mobile)	-5...+80 °C

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	MATERIAL -	FINISH -	DWN 16NOV2013 SATHISH KUMAR .G CHK 16NOV2013 B.VELDHOVEN APVD 16NOV2013 A.VAN ZANDVOORT	NAME M12 X 1.0 STRAIGHT SOCKET PIGT A
				PRODUCT SPEC 108-19483	SIZE A3
		WEIGHT 114-32127		APPLICATION SPEC 114-32127	CAGE CODE 00779
		CUSTOMER DRAWING		DRAWING NO C-2273023	RESTRICTED TO -
		SCALE NTS		SHEET 1 of 1	REV A3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2273023-3](#)