


THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	- , - .
© COPYRIGHT - By - ALL RIGHTS RESERVED.		

LOC H	DIST —	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	INITIAL RELEASE	15NOV2013	YC	BvH
			A1	ECR-14-011671	16AUG2014	GSK	BvH

NOTES:

Tolerances cable lengths:

0m to 0.5m	+30mm
0.5m to 1.0m	+50mm
1.0m to 3.0m	+100mm
< 3.0m	+1.5%



TECHNICAL DATA	
Operating voltage	max. 60 V AC/DC
Operating current per contact	max. 4 A
Locking of ports	Screw thread M12 x 1 mm (recommended torque 0.6 Nm) self-securing
Protection	IP65 and IP67 when plugged and screwed down (EN 60529)

PUR CABLE	
No./diameter of wires	4 x 0.34 mm ²
Wire isolation	PVC (br, wh, bl, bk)
C-track properties	
Jacket	PUR/PVC (UL/CSA)
Outer diameter	approx. 5.9 mm
Bend radius (moving)	15 x outer diameter
Temperature range (fixed)	-30...+80 °C
Temperature range (mobile)	-5...+70 °C

PVC CABLE	
No./diameter of wires	4 x 0.34 mm ²
Wire isolation	PVC (br, wh, bl, bk)
C-track properties	
Jacket	PVC (UL/CSA)
Outer diameter	approx. 5.9 mm
Bend radius (moving)	15 x outer diameter
Temperature range (fixed)	−30...+80 °C
Temperature range (mobile)	−5...+70 °C

4 pos	10mtr	PVC	GREY	1-2273044-4	4x22AWG PVC 10.0m	8
	5mtr			1-2273044-3	4x22AWG PVC 5.0m	7
	3mtr			1-2273044-2	4x22AWG PVC 3.0m	6
	1.5mtr			1-2273044-1	4x22AWG PVC 1.5m	5
4 pos	10mtr	PUR	GREY	2273044-4	4x22AWG PUR 10.0m	4
	5mtr			2273044-3	4x22AWG PUR 5.0m	3
	3mtr			2273044-2	4x22AWG PUR 3.0m	2
	1.5mtr			2273044-1	4x22AWG PUR 1.5m	1
	LENGTH”L”	MATERIAL	JACKET COLOR	TE PN	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN YATHISH.C 15NOV2013		 TE Connectivity	
DIMENSIONS: mm		CHK B.VELDHOFEN 15NOV2013			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD A.VAN ZANDVOORT 15NOV2013		NAME	
		PRODUCT SPEC 108-19483		M12 X 1.0 STRAIGHT PLUG PIGT SHLD A	
		APPLICATION SPEC 114-32127			
MATERIAL -		FINISH -		SIZE A3	CAGE CODE 00779
		WEIGHT -		DRAWING NO C-2273044	
CUSTOMER DRAWING				SCALE NTS	SHEET 1 OF 1
				REV A1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2273044-2](#)