



TAPING STYLE B: 4POS. THRU 8POS.



TAPING STYLE A: 2POS. AND 3POS.



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± 0.50

1 PLC ± 0.30

2 PLC ± 0.20

3 PLC $\pm$

4 PLC $\pm$

ANGLES $\pm 3^\circ$

FINISH

MATERIAL

SEE TABLE 1

DWN OTTO CHEN 15FEB2016

CHK DANIEL Z 16FEB2016

APVD DANIEL Z 16FEB2016

PRODUCT SPEC 108-2418

APPLICATION SPEC 114-13315

WEIGHT -

CUSTOMER DRAWING

TABLE 1

NO.	NAME	MATERIAL
①	HDR HOUSING	THERMOPLASTIC, UL94V-0
②	POST CONTACT	BRASS, NICKEL UNDER PLATING, TIN PLATING ON PIN AREA
③	RADIAL PIN	
④	RADIAL TAPE	THERMAL PAPER
⑤	BACKING PAPER	CRAFT PAPER

STE

TE Connectivity

NAME

HEADER ASSEMBLY, VERTICAL ECONOMY POWER, 2.5mm CENTERLINE TAPING VERSION

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A200779

C-2299683

-

-

SCALE

N/A

SHEET 1 OF 2

REV C1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT copyright.dBTe

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

2POS.

DIM.D

2.5±1.0

6.35±0.70

12.7±0.3
PITCH

3POS.

4POS.

5POS.

6POS.

7POS.

8POS.

5POS. WITH KINK

SEE DETAIL A

1.00±0.15

0.76 REF

2.00±0.15

DETAIL A
SCALE 20:1

B	450	WITHOUT KINK	2.50	17.50	20.83	22.50	8	2299683-8	1-2299683-8	2-2299683-8	3-2299683-8	4-2299683-8	5-2299683-8
B	450	WITHOUT KINK	2.50	15.00	18.33	20.00	7	2299683-7	1-2299683-7	2-2299683-7	3-2299683-7	4-2299683-7	5-2299683-7
B	450	WITHOUT KINK	2.50	12.50	15.83	17.50	6	2299683-6	1-2299683-6	2-2299683-6	3-2299683-6	4-2299683-6	5-2299683-6
B	450	WITHOUT KINK	2.50	10.00	13.33	15.00	5	2299683-9	1-2299683-9	2-2299683-9	3-2299683-9	4-2299683-9	5-2299683-9
B	450	WITH KINK	2.50	10.00	13.33	15.00	5	2299683-5	1-2299683-5	2-2299683-5	3-2299683-5	4-2299683-5	5-2299683-5
B	450	WITHOUT KINK	2.50	7.50	10.83	12.50	4	2299683-4	1-2299683-4	2-2299683-4	3-2299683-4	4-2299683-4	5-2299683-4
A	900	WITHOUT KINK	2.50	5.00	8.33	10.00	3	2299683-3	1-2299683-3	2-2299683-3	3-2299683-3	4-2299683-3	5-2299683-3
A	900	WITHOUT KINK	1.60	2.50	5.83	7.50	2	2299683-2	1-2299683-2	2-2299683-2	3-2299683-2	4-2299683-2	5-2299683-2
A	900	WITHOUT KINK	0.85	2.50	5.83	7.50	2	2299683-1	1-2299683-1	2-2299683-1	3-2299683-1	4-2299683-1	5-2299683-1
TAPING STYLE	QTY	SOLDER TAIL SHAPE	DIM.D	DIM.C	DIM.B	DIM.A	POS.	PART NO (NATURAL COLOR)	PART NO (RED COLOR)	PART NO (BLUE COLOR)	PART NO (BLACK COLOR)	PART NO (YELLOW COLOR)	PART NO (GREEN COLOR)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
SEE TABLE 1

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±0.50

1 PLC ±0.30

2 PLC ±0.20

3 PLC ±

4 PLC ±

ANGLES ±3°

FINISH

DWN 15FEB2016 OTTO CHEN

CHK 16FEB2016 DANIEL Z

APVD 16FEB2016 DANIEL Z

PRODUCT SPEC 108-2418

APPLICATION SPEC 114-13315

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

NAME
HEADER ASSEMBLY, VERTICAL
ECONOMY POWER, 2.5mm CENTERLINE
TAPING VERSION

SIZE A2

CAGE CODE 00779

DRAWING NO C-2299683

RESTRICTED TO -

SCALE N/A

SHEET 2 OF 2

REV C1

1471-9 (3/13)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[4-2299683-8](#)