






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

SUGGESTED PCB LAYOUT




UNIT:mm / INCH
TOLERANCES: ±0.10 / 0.004
ONLY FOR THIS VIEW


CONNECTOR BOUNDRY



METAL PANEL



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. SHARMA 27AUG2016		TE Connectivity Ltd.					
		CHK O. WIBORG 27AUG2016							
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	APVD J. DE BRUIJN 27AUG2016		NAME RJ45 JACK INT.MAG. 10/100 LED 1x2 INV.					
		PRODUCT SPEC 108-94552							
		APPLICATION SPEC 114-94447		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO —		
		WEIGHT		A3	00779	C-2301996-5			
MATERIAL 		FINISH 		CUSTOMER DRAWING			SCALE 3:1	SHEET 2 OF 3	REV B1



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2301996-5](#)