







2302494-1
ASSEMBLED ISOMETRIC VIEW SHOWN




2302494-1
EXPLODED ISOMETRIC VIEW SHOWN




2302494-2
ASSEMBLED ISOMETRIC VIEW SHOWN





2302494-2
EXPLODED ISOMETRIC VIEW SHOWN



2302488-3
ASSEMBLED ISOMETRIC VIEW SHOWN



2302494-3
EXPLODED ISOMETRIC VIEW SHOWN






2302494-1
ASSEMBLED VIEW SHOWN
DIMENSIONS SHOWN TYPICAL FOR 2302494-1 AND -3



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
2	A	RELEASED PER ECO-16-008203	01JUN2016	JM	RB
	A2	REV PER ECO-16-013256	08SEP2016	JM	RB

- 1 MATERIAL: NYLON MOLDING COMPOUND, BLACK, PA66/6.
- 2 BACKSHELL DESIGNED SUCH THAT TWO HALVES ATTACH TO ONE ANOTHER AND CLAMP AROUND THE CONNECTOR COVER.
- 3 ELBOW DESIGNED SUCH THAT TWO HALVES ATTACH TO ONE ANOTHER AND CLAMP AROUND THE BACKSHELL COLLAR.
- 4 DIMENSIONS TO BE MEASURED WHEN ELBOWS AND BACKSHELLS ASSEMBLED.
- 5 PRODUCT WEIGHTS:
2302494-1: 13.80g ASSEMBLED
2302494-2: 14.25g ASSEMBLED
2302494-3: 14.00g ASSEMBLED
- 6 4MM WIDE SLOTS FOR TIE WRAP TO SECURE HARNESS WIRES (-1 ONLY).
- 7 HEAT SHRINK TUBING FEATURE (-1 AND -3 ONLY).
8. INSTRUCTION SHEET: 408-151043.
9. CONDUIT PROFILE: NORMAL ONLY.



2302494-2
ASSEMBLED VIEW SHOWN
DIMENSIONS SHOWN FOR 2302494-2 ONLY



776494-X 776532-X	NC16	NW13	2302494-3
	NC20	NW17	2302494-2
	SMOOTH	SMOOTH	2302494-1
FITS ON PLUG ASSY	CORREGATE NC	CORREGATE NW	PART NUMBER
CONDUIT SIZE			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J MCNEAL 13APR2016	TE Connectivity	
DIMENSIONS: mm[INCHES]		CHK R BALTER 13APR2016		
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
	0 PLC ±		PRODUCT SPEC	
	1 PLC ±		108-151043	
	2 PLC ±		APPLICATION SPEC	
MATERIAL		WEIGHT	SIZE	CAGE CODE
1		5	A1	00779
CUSTOMER DRAWING		DRAWING NO		RESTRICTED TO
		C=2302494		-
		SCALE		SHEET
		3:2		1 OF 1
				REV
				A2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2302494-1](#)