











REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW RELEASE	12FEB2020	L.C	D.2



- △ MATERIAL: PA66, UL94V-0, COLOR: NATURAL
2. APPLICABLE CONTACT P/N
2321928-1 OR 1-2321928-1
3. MATING CONNECTOR P/N
PLUG HSG: 2321918-*
TPA (OPTIONAL): 2321927-*
GANG SEAL: 2321922-*
4. COMPLY WITH GLOW WIRE REQUIREMENTS FOR PARTS OF NON-METALLIC MATERIAL SUPPORTING A CURRENT-CARRYING CONNECTION DETAILED IN IEC 60335-1, SECTION 30(GWT)
- △ PRELIMINARY PART - NOT RELEASED FOR PRODUCTION
THIS PART HAS NOT COMPLETED QUALIFICATION TESTING



27.4	17.50	1.25	29.98	22.90	22.40	1*8	△ 2321926-8
24.9	15.00	0	27.48	20.40	19.90	1*7	△ 2321926-7
22.4	12.50	1.25	24.98	17.90	17.40	1*6	2321926-6
19.9	10.00	0	22.48	15.40	14.90	1*5	2321926-5
17.4	7.50	1.25	19.98	12.90	12.40	1*4	2321926-4
14.9	5.00	0	17.48	10.40	9.90	1*3	2321926-3
12.4	2.50	1.25	14.98	7.90	7.40	1*2	2321926-2
DIM "F"	DIM "E"	DIM "D"	DIM "C"	DIM "B"	DIM "A"	POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN B. WEAVER CHK S. FERNANDES APVD C. YI	15FEB2019 15FEB2019 15FEB2019	 TE Connectivity			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		NAME SDL 25 Panel			
		0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES FINISH	± ± ±0.25 ± ± ± ±	108-143069 APPLICATION SPEC 114-143067		SIZE A1	CAGE CODE 00779	DRAWING NO C=2321926	RESTRICTED TO -
MATERIAL 		-		WEIGHT -		SCALE 3:1			
CUSTOMER DRAWING						SHEET 1 OF 1		REV A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2321926-2](#)