

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - A

ALL RIGHTS RESERVED.

PROJECT

PRJ-14-000004825

PART NO.

X-2322330-X




DESCRIPTION

M12 D-4 CODE CABLE ASSY. (PLUG-PLUG) CAT 5E

CUSTOMER

GENERAL MARKET


| REVISIONS |     |                                       |           |     |      |
|-----------|-----|---------------------------------------|-----------|-----|------|
| P         | LTR | DESCRIPTION                           | DATE      | DWN | APVD |
|           | A1  | INTRODUCTION OF NEW DASH VARIANT, -99 | 24SEP2019 | GK  | SE   |




| WIRING TABLE |  |             |  |     |
|--------------|--|-------------|--|-----|
| PIN          |  | WIRE COLORS |  | PIN |
| 1            |  | YELLOW      |  | 1   |
| 2            |  | WHITE       |  | 2   |
| 3            |  | ORANGE      |  | 3   |
| 4            |  | BLUE        |  | 4   |

M12 D-CODE CABLE ASSEMBLY  
(STRAIGHT CONNECTOR)

| SL.NO | CODE    | ASSY. PART NO. | M12 CONNECTOR PART NO.    | DESCRIPTION                                   | CABLE TYPE      | CABLE PART NO. | CABLE LENGTH "L" IN "m" | NO. OF POSITIONS |
|-------|---------|----------------|---------------------------|-----------------------------------------------|-----------------|----------------|-------------------------|------------------|
| 1     | D4-CODE | 9-2322330-9    | 2-2823445-1<br>(STRAIGHT) | M12 D-4-M CABLE ASSY. (PLUG-PLUG) 0.5M CABLE  | TE CAT 5E CABLE | 2320808-1      | 0.5                     | 4                |
| 2     | D4-CODE | 2322330-1      |                           | M12 D-4-M CABLE ASSY. (PLUG-PLUG) 1M CABLE    |                 |                | 1.0                     | 4                |
| 3     | D4-CODE | 2322330-2      |                           | M12 D-4-M CABLE ASSY. (PLUG-PLUG) 1.5M CABLE  |                 |                | 1.5                     | 4                |
| 4     | D4-CODE | 2322330-3      |                           | M12 D-4-M CABLE ASSY. (PLUG-PLUG) 2M CABLE    |                 |                | 2.0                     | 4                |
| 5     | D4-CODE | 2322330-4      |                           | M12 D-4-M CABLE ASSY. (PLUG-PLUG) 2.5M CABLE  |                 |                | 2.5                     | 4                |
| 6     | D4-CODE | 2322330-5      |                           | M12 D-4-M CABLE ASSY. (PLUG-PLUG) 3M CABLE    |                 |                | 3.0                     | 4                |
| 7     | D4-CODE | 2322330-6      |                           | M12 D-4-M CABLE ASSY. (PLUG-PLUG) 3.5M CABLE  |                 |                | 3.5                     | 4                |
| 8     | D4-CODE | 2322330-7      |                           | M12 D-4-M CABLE ASSY. (PLUG-PLUG) 4M CABLE    |                 |                | 4.0                     | 4                |
| 9     | D4-CODE | 2322330-8      |                           | M12 D-4-M CABLE ASSY. (PLUG-PLUG) 4.5M CABLE  |                 |                | 4.5                     | 4                |
| 10    | D4-CODE | 2322330-9      |                           | M12 D-4-M CABLE ASSY. (PLUG-PLUG) 5M CABLE    |                 |                | 5.0                     | 4                |
| 11    | D4-CODE | 1-2322330-0    |                           | M12 D-4-M CABLE ASSY. (PLUG-PLUG) 5.5M CABLE  |                 |                | 5.5                     | 4                |
| 12    | D4-CODE | 1-2322330-1    |                           | M12 D-4-M CABLE ASSY. (PLUG-PLUG) 6M CABLE    |                 |                | 6.0                     | 4                |
| 13    | D4-CODE | 1-2322330-2    |                           | M12 D-4-M CABLE ASSY. (PLUG-PLUG) 6.5M CABLE  |                 |                | 6.5                     | 4                |
| 14    | D4-CODE | 1-2322330-3    |                           | M12 D-4-M CABLE ASSY. (PLUG-PLUG) 7M CABLE    |                 |                | 7.0                     | 4                |
| 15    | D4-CODE | 1-2322330-4    |                           | M12 D-4-M CABLE ASSY. (PLUG-PLUG) 7.5M CABLE  |                 |                | 7.5                     | 4                |
| 16    | D4-CODE | 1-2322330-5    |                           | M12 D-4-M CABLE ASSY. (PLUG-PLUG) 8M CABLE    |                 |                | 8.0                     | 4                |
| 17    | D4-CODE | 1-2322330-6    |                           | M12 D-4-M CABLE ASSY. (PLUG-PLUG) 8.5M CABLE  |                 |                | 8.5                     | 4                |
| 18    | D4-CODE | 1-2322330-7    |                           | M12 D-4-M CABLE ASSY. (PLUG-PLUG) 9M CABLE    |                 |                | 9.0                     | 4                |
| 19    | D4-CODE | 1-2322330-8    |                           | M12 D-4-M CABLE ASSY. (PLUG-PLUG) 9.5M CABLE  |                 |                | 9.5                     | 4                |
| 20    | D4-CODE | 1-2322330-9    |                           | M12 D-4-M CABLE ASSY. (PLUG-PLUG) 10M CABLE   |                 |                | 10.0                    | 4                |
| 21    | D4-CODE | 2-2322330-0    |                           | M12 D-4-M CABLE ASSY. (PLUG-PLUG) 10.5M CABLE |                 |                | 10.5                    | 4                |
| 22    | D4-CODE | 2-2322330-1    |                           | M12 D-4-M CABLE ASSY. (PLUG-PLUG) 11M CABLE   |                 |                | 11.0                    | 4                |
| 23    | D4-CODE | 2-2322330-2    |                           | M12 D-4-M CABLE ASSY. (PLUG-PLUG) 11.5M CABLE |                 |                | 11.5                    | 4                |
| 24    | D4-CODE | 2-2322330-3    |                           | M12 D-4-M CABLE ASSY. (PLUG-PLUG) 12M CABLE   |                 |                | 12.0                    | 4                |
| 25    | D4-CODE | 2-2322330-4    |                           | M12 D-4-M CABLE ASSY. (PLUG-PLUG) 12.5M CABLE |                 |                | 12.5                    | 4                |
| 26    | D4-CODE | 2-2322330-5    |                           | M12 D-4-M CABLE ASSY. (PLUG-PLUG) 13M CABLE   |                 |                | 13.0                    | 4                |
| 27    | D4-CODE | 2-2322330-6    |                           | M12 D-4-M CABLE ASSY. (PLUG-PLUG) 13.5M CABLE |                 |                | 13.5                    | 4                |
| 28    | D4-CODE | 2-2322330-7    |                           | M12 D-4-M CABLE ASSY. (PLUG-PLUG) 14M CABLE   |                 |                | 14.0                    | 4                |
| 29    | D4-CODE | 2-2322330-8    |                           | M12 D-4-M CABLE ASSY. (PLUG-PLUG) 14.5M CABLE |                 |                | 14.5                    | 4                |
| 30    | D4-CODE | 2-2322330-9    |                           | M12 D-4-M CABLE ASSY. (PLUG-PLUG) 15M CABLE   |                 |                | 15.0                    | 4                |
| 31    | D4-CODE | 3-2322330-0    |                           | M12 D-4-M CABLE ASSY. (PLUG-PLUG) 15.5M CABLE |                 |                | 15.5                    | 4                |
| 32    | D4-CODE | 3-2322330-1    |                           | M12 D-4-M CABLE ASSY. (PLUG-PLUG) 16M CABLE   |                 |                | 16.0                    | 4                |
| 33    | D4-CODE | 3-2322330-2    |                           | M12 D-4-M CABLE ASSY. (PLUG-PLUG) 16.5M CABLE |                 |                | 16.5                    | 4                |
| 34    | D4-CODE | 3-2322330-3    |                           | M12 D-4-M CABLE ASSY. (PLUG-PLUG) 17M CABLE   |                 |                | 17.0                    | 4                |
| 35    | D4-CODE | 3-2322330-4    |                           | M12 D-4-M CABLE ASSY. (PLUG-PLUG) 17.5M CABLE |                 |                | 17.5                    | 4                |
| 36    | D4-CODE | 3-2322330-5    |                           | M12 D-4-M CABLE ASSY. (PLUG-PLUG) 18M CABLE   |                 |                | 18.0                    | 4                |
| 37    | D4-CODE | 3-2322330-6    |                           | M12 D-4-M CABLE ASSY. (PLUG-PLUG) 18.5M CABLE |                 |                | 18.5                    | 4                |
| 38    | D4-CODE | 3-2322330-7    |                           | M12 D-4-M CABLE ASSY. (PLUG-PLUG) 19M CABLE   |                 |                | 19.0                    | 4                |
| 39    | D4-CODE | 3-2322330-8    |                           | M12 D-4-M CABLE ASSY. (PLUG-PLUG) 19.5M CABLE |                 |                | 19.5                    | 4                |
| 40    | D4-CODE | 3-2322330-9    |                           | M12 D-4-M CABLE ASSY. (PLUG-PLUG) 20M CABLE   |                 |                | 20.0                    | 4                |



SECTIONAL  
PICTORIAL VIEW OF  
THE CABLE



PICTORIAL  
VIEW

| SL.NO. | PART NO.    | DESCRIPTION                    | QTY                   |
|--------|-------------|--------------------------------|-----------------------|
| 1      | 2-2823445-1 | M12 D-CODED M-8 MALE CONNECTOR | 2                     |
| 2      | 2320808-1   | TE CAT 5E CABLE (COLOR: BLUE)  | METER<br>(REF. TABLE) |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN KIRAN K 07JUL2017

CHK KIRAN K 07JUL2017

APVD E STELLINGA 07JUL2017

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH -

TE Connectivity

M12 D-4-M CODE CABLE ASSEMBLY CAT 5E (PLUG-PLUG)

SIZE A2 CAGE CODE 00779 DRAWING NO C-2322330

CUSTOMER DRAWING

RESTRICTED TO -

SCALE NTS SHEET 1 OF 1 REV A1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3-2322330-5](#)