





SL.NO	CODE	ASSY. PART NO.	M12 CONNECTOR 1 PART NO.	M12 CONNECTOR 2 PART NO.	DESCRIPTION	CABLE TYPE	CABLE PART NO.	CABLE LENGTH "L" IN "m"	NO. OF POSITIONS
1	D4-CODE	2322422-1	2-2823445-1 (STRAIGHT)	1-2823588-3 (RIGHT ANGLE)	M12 D-4-M CABLE ASSY. (PLUG-PLUG) 1M CABLE	TE CAT 5E CABLE	2320808-1	1.0	4
2	D4-CODE	2322422-2			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 1.5M CABLE			1.5	4
3	D4-CODE	2322422-3			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 2M CABLE			2.0	4
4	D4-CODE	2322422-4			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 2.5M CABLE			2.5	4
5	D4-CODE	2322422-5			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 3M CABLE			3.0	4
6	D4-CODE	2322422-6			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 3.5M CABLE			3.5	4
7	D4-CODE	2322422-7			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 4M CABLE			4.0	4
8	D4-CODE	2322422-8			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 4.5M CABLE			4.5	4
9	D4-CODE	2322422-9			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 5M CABLE			5.0	4
10	D4-CODE	1-2322422-0			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 5.5M CABLE			5.5	4
11	D4-CODE	1-2322422-1			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 6M CABLE			6.0	4
12	D4-CODE	1-2322422-2			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 6.5M CABLE			6.5	4
13	D4-CODE	1-2322422-3			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 7M CABLE			7.0	4
14	D4-CODE	1-2322422-4			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 7.5M CABLE			7.5	4
15	D4-CODE	1-2322422-5			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 8M CABLE			8.0	4
16	D4-CODE	1-2322422-6			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 8.5M CABLE			8.5	4
17	D4-CODE	1-2322422-7			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 9M CABLE			9.0	4
18	D4-CODE	1-2322422-8			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 9.5M CABLE			9.5	4
19	D4-CODE	1-2322422-9			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 10M CABLE			10.0	4
20	D4-CODE	2-2322422-0			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 10.5M CABLE			10.5	4
21	D4-CODE	2-2322422-1			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 11M CABLE			11.0	4
22	D4-CODE	2-2322422-2			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 11.5M CABLE			11.5	4
23	D4-CODE	2-2322422-3			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 12M CABLE			12.0	4
24	D4-CODE	2-2322422-4			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 12.5M CABLE			12.5	4
25	D4-CODE	2-2322422-5			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 13M CABLE			13.0	4
26	D4-CODE	2-2322422-6			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 13.5M CABLE			13.5	4
27	D4-CODE	2-2322422-7			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 14M CABLE			14.0	4
28	D4-CODE	2-2322422-8			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 14.5M CABLE			14.5	4
29	D4-CODE	2-2322422-9			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 15M CABLE			15.0	4
30	D4-CODE	3-2322422-0			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 15.5M CABLE			15.5	4
31	D4-CODE	3-2322422-1			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 16M CABLE			16.0	4
32	D4-CODE	3-2322422-2			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 16.5M CABLE			16.5	4
33	D4-CODE	3-2322422-3			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 17M CABLE			17.0	4
34	D4-CODE	3-2322422-4			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 17.5M CABLE			17.5	4
35	D4-CODE	3-2322422-5			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 18M CABLE			18.0	4
36	D4-CODE	3-2322422-6			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 18.5M CABLE			18.5	4
37	D4-CODE	3-2322422-7			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 19M CABLE			19.0	4
38	D4-CODE	3-2322422-8			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 19.5M CABLE			19.5	4
39	D4-CODE	3-2322422-9			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 20M CABLE			20.0	4



SECTIONAL PICTORIAL VIEW OF THE CABLE

PICTORIAL VIEW

SL.NO.	PART NO.	DESCRIPTION	QTY
1	2-2823445-1	M12 D-4 CODED MALE CONNECTOR	1
2	2320808-1	TE CAT 5E CABLE (COLOR: BLUE)	METER (REF. TABLE)
3	1-2823588-3	M12 D-4 CODED MALE 90° CONNECTOR	1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

KIRAN_K

07JUL2017

CHK

KIRAN_K

07JUL2017

APVD

E_STELLINGA

07JUL2017

TE Connectivity

M12 D-4-M CODE CABLE ASSEMBLY CAT 5E (PLUG-PLUG)

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±	-
1 PLC	±	-
2 PLC	±	-
3 PLC	±	-
4 PLC	±	-
ANGLES	±	-

MATERIAL

-

FINISH

-

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

-

SIZE

A2

CAGE CODE

00779

DRAWING NO

C=2322422

RESTRICTED TO

-

CUSTOMER DRAWING

SCALE

NTS

SHEET

1 OF 1

REV

A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-2322422-8](#)