



P	LTR	DESCRIPTION	DATE	DWN	APVD
	B1	ECR-19-013004	26AUG2019	SR	JL
	B2	ECR-20-000233	13JAN2020	SB	JL
	B3	ECR-20-000836	23JAN2020	SB	JL
	B4	ECR-20-002949	02MAR2020	SR	JL

- 1 MATERIALS:
HOLDER: PBT ,COLOR: NATURAL;
CONTACTS: COPPER ALLOY, Au/Ni PLATING (LED INTERFACE)
2. FOR SOLID, FUSED AND STRANDED CONDUCTOR WIRE TYPES AWG 18 AND 20
3. WIRE STRIP LENGTH: 11-12mm
4. MAX. WIRE INSULATION OUTER DIA: Ø2,3mm
5. RECOMMENDED SCREW TORQUE: SEE APPLICATION SPECIFICATION 114-133107.
6. SCREWS TO BE USED: M3, #4-40
7. LED MATING ON 2 CORNERS WITH ADHESIVE TAPE 3M 9472LE 300LSE.
- 8 LAYOUTS ON SHEET 3
9. FOR COB-TO-HOLDER CROSS REFERENCE,
REFER TO APPLICATION SPECIFICATION 114-32208




PAN HEAD
SCALE 3:1



COUNTERSINK
SCALE 3:1

A	PAN HEAD	4-2325811-2
C	COUNTERSINK	3-2325811-1
C	PAN HEAD	2-2325811-1
B	COUNTERSINK	1-2325811-3
B	PAN HEAD	2325811-3
A	COUNTERSINK	1-2325811-2
A	PAN HEAD	2325811-2
LED LAYOUT 8	DESCRIPTION	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. DAILY 20DEC2017		 TE Connectivity			
		CHK J. LATORRE 20DEC2017					
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.2 2 PLC ±0.13 3 PLC ± 4 PLC ± ANGLES ±2° FINISH - -		NAME LED HOLDER, 20x24 LUMAWISE Z45 LED -			
				PRODUCT SPEC 108-133062			
				APPLICATION SPEC 114-133107			
MATERIAL 		WEIGHT -		SIZE A2	CAGE CODE 00779	DRAWING NO C-2325811	RESTRICTED TO -
CUSTOMER DRAWING				SCALE 3:1	SHEET 1 OF 4	REV B4	



SECTION X - X

2325811-2 SHOWN
SCALE 3:1



2-2325811-1
AND
3-2325811-1
ONLY
(TAPE REMOVED)
SCALE 3:1

SECTION X - X
1-2325811-2 SHOWN
SCALE 3:1



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

D



C

B

A



SECTION Y-Y
4-2325811-2 AS SHOWN




D

C

B

A

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. DAILY 20DEC2017	 TE Connectivity			
		CHK J. LATORRE 20DEC2017				
DIMENSIONS:		APVD -	NAME LED HOLDER, 20x24 LUMAWISE Z45 LED			
mm		PRODUCT SPEC 108-133062				
		APPLICATION SPEC 114-133107				
MATERIAL		WEIGHT -	SIZE A200779	CAGE CODE C-2325811	DRAWING NO	RESTRICTED TO
		CUSTOMER DRAWING	SCALE 3:1	SHEET 3 OF 4	REV B4	



THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		20	
©	COPYRIGHT 20	BY -	ALL RIGHTS RESERVED.		

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

LED SUBSTRATE LAYOUT A
TOP SIDE OF BOARD

2.83

3.08

CONTACT POINT

20.0±0.2

2.83

2.78

24.0±0.2

LED SUBSTRATE LAYOUT B
TOP SIDE OF BOARD

3.37

1.88

CONTACT POINT

20.0±0.2

3.00

1.91

24.0±0.2

LED SUBSTRATE LAYOUT C
TOP SIDE OF BOARD

2.83

3.58

CONTACT POINT

20.0±0.2

2.42

3.62

24.0±0.2

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. DAILY 20DEC2017	TE Connectivity			
DIMENSIONS:		CHK J. LATORRE 20DEC2017				
mm		APVD -	NAME LED HOLDER, 20x24 LUMAWISE Z45 LED			
		PRODUCT SPEC 108-133062	SIZE A200779		CAGE CODE C-2325811	
		APPLICATION SPEC 114-133107				
		MATERIAL -	WEIGHT -	DRAWING NO -		RESTRICTED TO -
-	-	CUSTOMER DRAWING		SCALE 3:1	SHEET 4 OF 4	REV B4
TOLERANCES UNLESS OTHERWISE SPECIFIED:						
0 PLC ±-						
1 PLC ±0.2						
2 PLC ±0.13						
3 PLC ±-						
4 PLC ±-						
ANGLES ±2°						
FINISH						
-						
-						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-2325811-1](#)