


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASE PER ECR-19-000700	16JAN2019	JS	DD
	A1	REVISED PER ECR-19-003367	05MAR2019	SR	DD
	A2	REVISED PER ECR-19-008525	31MAY2019	SR	DD
	A3	REVISED PER ECR-20-002559	26FEB2020	SB	DD



- 1
- MATERIALS:
HOUSING: PBT
LINE VOLTAGE CONTACTS: COPPER ALLOY
SHORTING CLIP: COPPER ALLOY
GASKET: NBR/PVC BLEND
O-RING: SILICONE RUBBER
COVER: PBT, UL UV-f1 RATED
- 2
- FINISH:
LINE VOLTAGE CONTACTS: MATTE TIN PLATE
- 3
- MATING INTERFACE PER ANSI C136.10.
- 4
- ADHESIVE BACKED GASKET APPLIED
5.
- THIS PRODUCT HAS NOT COMPLETED VALIDATION TESTING.
- 6
- PRODUCT INFORMATION LABEL
- 7
- 157 JOULE MOV WITH A MAX SURGE CURRENT OF 4500A AND A MAX CLAMPING VOLTAGE OF 1355V.

RED	OPEN	2328118-3
BLACK	SHORTING AND SURGE PROTECTION	2328118-2
BLACK	SHORTING	2328118-1
CAP COLOR	DESCRIPTION	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
C. DAILY
CHK
M. STOLLER
APVD
-

23JAN2018
23JAN2018

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±0.2
2 PLC ±0.13
3 PLC ±-
4 PLC ±-
ANGLES ±1°
FINISH -

MATERIAL
SEE TABLE
-

PRODUCT SPEC
108-133113

APPLICATION SPEC
408-133113

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
ASSEMBLY,
LUMAWISE SHORTING CAP
-

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-2328118

RESTRICTED TO
-

SCALE
7:4

SHEET
1 OF 1

REV
A3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2328118-2](#)