







REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	REVISED PER ECR-18-017862	22NOV2018	SR	DD
	B	REVISED PER ECR-19-008311	06JUN2019	SR	DD
	B1	REVISED PER ECR-19-015297	01OCT2019	SB	DD
	B2	REVISED PER ECR-20-007067	24JUN2020	SB	DD



2328823-1 AND 1-2328823-1
SHOWN



2328823-2 AND 1-2328823-2
SHOWN



2328823-3 AND 1-2328823-3
SHOWN

NOTES:

- 1 MATERIAL:
-POLYCARBONATE COLOR: SEE TABLE
2. MUST COMPLY WITH DIRECTIVE 2002/95/EC (ROHS)
3. MODULE BASE TE P/N: 2213831-1
4. PACKAGED 24 PER PLASTIC TRAY
DIM X = 33.43 AND 43.43 - 7 TRAYS PER BOX
DIM X = 58.43 - 5 TRAYS PER BOX

NO	26%	TRANSLUCENT GRAY	58.43	4-2328823-3
NO	26%	TRANSLUCENT GRAY	43.43	4-2328823-2
NO	26%	TRANSLUCENT GRAY	33.43	4-2328823-1
YES	78%	TRANSPARENT CLEAR	58.43	3-2328823-3
YES	78%	TRANSPARENT CLEAR	43.43	3-2328823-2
YES	78%	TRANSPARENT CLEAR	33.43	3-2328823-1
YES	24%	TRANSPARENT SMOKE	58.43	2-2328823-3
YES	24%	TRANSPARENT SMOKE	43.43	2-2328823-2
YES	24%	TRANSPARENT SMOKE	33.43	2-2328823-1
NO	78%	TRANSPARENT CLEAR	58.43	1-2328823-3
NO	78%	TRANSPARENT CLEAR	43.43	1-2328823-2
NO	78%	TRANSPARENT CLEAR	33.43	1-2328823-1
NO	24%	TRANSPARENT SMOKE	58.43	2328823-3
NO	24%	TRANSPARENT SMOKE	43.43	2328823-2
NO	24%	TRANSPARENT SMOKE	33.43	2328823-1
IDENTIFICATION MARKINGS	APPROX. LIGHT TRANSMISSION	COLOR	DIM X	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
SEE TABLE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-
1 PLC ±0.2
2 PLC ±0.10
3 PLC ±-
4 PLC ±-
ANGLES ±1°
FINISH -
-

DWN
C. DAILY
10JAN2018

CHK
MSTOLLER
10JAN2018

APVD
-

PRODUCT SPEC
108-133073

APPLICATION SPEC
114-133074

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
DOME, LUMAWISE ENDURANCE S, 80mm

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-2328823

RESTRICTED TO


SCALE
1:1

SHEET
1



OF
2

REV
B2


P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-




POLARIZATION
FEATURES




2-2328823-1 AND 3-2328823-1
SHOWN



2-2328823-2 AND 3-2328823-2
SHOWN



2-2328823-3 AND 3-2328823-3
SHOWN



IDENTIFICATION MARKING PATTERN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. DAILY 10 JAN 2018	TE Connectivity			
		CHK M. STOLLER 10 JAN 2018				
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD -		NAME DOME, LUMAWISE ENDURANCE S, 80mm	
		0 PLC ± 1 PLC ±0.2 2 PLC ±0.10 3 PLC ± 4 PLC ± ANGLES ±1°	PRODUCT SPEC 108-133073		SIZE A200779	
MATERIAL SEE TABLE		FINISH -	APPLICATION SPEC 114-133074		CAGE CODE C-2328823	
			WEIGHT -		DRAWING NO C-2328823	
			CUSTOMER DRAWING		RESTRICTED TO	
			SCALE 1:1	SHEET 2 OF 2	REV B2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2328823-1](#)