

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


March ,2018.

© COPYRIGHT 2018 TE Connectivity Ltd.

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	23MAR2018	GK	ES

1x EARTH WASHER
(SUPPLIED LOOSE)ISO VIEW
SCALE 1:5

NOTES:

1. OPERATING FREQUENCIES:

CELLULAR: 698–960/1710–3800 MHz

WIFI : 2.4/5.0 GHz

GPS/GNSS: 1562–1612 MHz 26dB LNA

2. ALL MATERIALS SUPPLIED MUST BE RoHS2 (DIRECTIVE 2011/65/EU) COMPLIANT AND MUST NOT CONTAIN ANY SUBSTANCES OF VERY HIGH CONCERN (SVHCs) LISTED UNDER REACH OR POLY-AROMATIC HYDROCARBONS (PAHs), OR PERSISTENT ORGANIC POLLUTANTS (POPs) CONTROLLED BY THE STOCKHOLM CONVENTION.

3. PATTERN: OMNI-DIRECTIONAL.



4. POLARIZATION: VERTICAL

5. MAX. INPUT POWER: 25W.

6. OPERATING TEMPERATURE: –40°/+80°C(–40°/+176°F).

7. MATERIAL: ASA, EPDM, ALUMINUM ALLOY.

8. WEIGHT: 300.42g.



2332157-4	SHARK FIN MIMO 2/3/4G GPS 3X3WIFI 3M CAB	BLACK
2332157-3	SHARK FIN MIMO 2/3/4G GPS 2X2WIFI 3M CAB	
2332157-2	SHARK FIN MIMO 2/3/4G GPS 3M CABLES	
2332157-1	SHARK FIN MIMO 2/3/4G 3M CABLES	
TE P/N	DESCRIPTION	COLOR

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 12MAR2018

CHK GOPALAKRISHNA H.V.

E STELLINGA 12MAR2018

APVD E STELLINGA 12MAR2018

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING



TE Connectivity Ltd.

NAME MIMO COAX GPS/GNSS 2G/3G/4G WLAN SHARKFIN ANT


SIZE CAGE CODE DRAWING NO RESTRICTED TO

A3 00779 C=2332157

SCALE 1:1 SHEET 1 OF 1 REV A

DIMENSIONS:

mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:0 PLC ± 0.5
1 PLC ± 0.2
2 PLC ± 0.1
3 PLC ±
4 PLC ±
ANGLES ± 1°

MATERIAL

FINISH

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2332157-3](#)