

D

D

C


C

B

B

A

A



THIS PRODUCT HAS NOT
COMPLETED VALIDATION AND
QUALIFICATION TESTING

PRELIMINARY
NOT RELEASED FOR PRODUCTION

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TIM XUE 22MAR2018	TE Connectivity			
DIMENSIONS: mm		CHK SEAN HAN 22MAR2018				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD SEAN HAN 22MAR2018	NAME RECEPTACLE CONNECTOR, VERTICAL, 148 POSITION, SLIVER			
0 PLC ±0.15		PRODUCT SPEC	SIZE A2		CAGE CODE -	DRAWING NO. C-2332538
1 PLC ±0.15		APPLICATION SPEC	RESTRICTED TO		-	
2 PLC ±0.15		WEIGHT	SCALE 4:1		SHEET 2 OF 3	REV 3
3 PLC ±		CUSTOMER DRAWING				
4 PLC ±						
ANGLES ±						
FINISH						
MATERIAL						
-						
-						

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

P

LTR

DESCRIPTION

DATE

DWN

APVD

-

SEE SHEET 1

-

-

-

PIN #	DESCRIPTION	PIN #	DESCRIPTION
1	SIGNAL GROUND	148	SIGNAL GROUND
2	SIGNAL	147	SIGNAL
3	SIGNAL	146	SIGNAL
4	SIGNAL GROUND	145	SIGNAL GROUND
5	SIGNAL	144	SIGNAL
6	SIGNAL	143	SIGNAL
7	SIGNAL GROUND	142	SIGNAL GROUND
8	SIGNAL	141	SIGNAL
9	SIGNAL	140	SIGNAL
10	SIGNAL GROUND	139	SIGNAL GROUND
11	SIGNAL	138	SIGNAL
12	SIGNAL	137	SIGNAL
13	SIGNAL GROUND	136	SIGNAL GROUND
14	SIGNAL	135	SIGNAL
15	SIGNAL	134	SIGNAL
16	SIGNAL GROUND	133	SIGNAL GROUND
17	SIGNAL	132	SIGNAL
18	SIGNAL	131	SIGNAL
19	SIGNAL GROUND	130	SIGNAL GROUND
20	SIGNAL	129	SIGNAL
21	SIGNAL	128	SIGNAL
22	SIGNAL GROUND	127	SIGNAL GROUND
23	SIGNAL	126	SIGNAL
24	SIGNAL	125	SIGNAL
25	SIGNAL GROUND	124	SIGNAL GROUND
26	SIGNAL	123	SIGNAL
27	SIGNAL	122	SIGNAL
28	SIGNAL GROUND	121	SIGNAL GROUND
29	SIGNAL	120	SIGNAL
30	SIGNAL	119	SIGNAL
31	SIGNAL GROUND	118	SIGNAL GROUND
32	SIGNAL	117	SIGNAL
33	SIGNAL	116	SIGNAL
34	SIGNAL GROUND	115	SIGNAL GROUND
35	SIGNAL	114	SIGNAL
36	SIGNAL	113	SIGNAL
37	SIGNAL GROUND	112	SIGNAL GROUND

PIN #	DESCRIPTION	PIN #	DESCRIPTION
38	SIGNAL GROUND	111	SIGNAL GROUND
39	SIGNAL	110	SIGNAL
40	SIGNAL	109	SIGNAL
41	SIGNAL GROUND	108	SIGNAL GROUND
42	SIGNAL	107	SIGNAL
43	SIGNAL	106	SIGNAL
44	SIGNAL GROUND	105	SIGNAL GROUND
45	SIGNAL	104	SIGNAL
46	SIGNAL	103	SIGNAL
47	SIGNAL GROUND	102	SIGNAL GROUND
48	SIGNAL	101	SIGNAL
49	SIGNAL	100	SIGNAL
50	SIGNAL GROUND	99	SIGNAL GROUND
51	SIGNAL	98	SIGNAL
52	SIGNAL	97	SIGNAL
53	SIGNAL GROUND	96	SIGNAL GROUND
54	SIGNAL	95	SIGNAL
55	SIGNAL	94	SIGNAL
56	SIGNAL GROUND	93	SIGNAL GROUND
57	SIGNAL	92	SIGNAL
58	SIGNAL	91	SIGNAL
59	SIGNAL GROUND	90	SIGNAL GROUND
60	SIGNAL	89	SIGNAL
61	SIGNAL	88	SIGNAL
62	SIGNAL GROUND	87	SIGNAL GROUND
63	SIGNAL	86	SIGNAL
64	SIGNAL	85	SIGNAL
65	SIGNAL GROUND	84	SIGNAL GROUND
66	SIGNAL	83	SIGNAL
67	SIGNAL	82	SIGNAL
68	SIGNAL GROUND	81	SIGNAL GROUND
69	SIGNAL	80	SIGNAL
70	SIGNAL	79	SIGNAL
71	SIGNAL GROUND	78	SIGNAL GROUND
72	SIGNAL	77	SIGNAL
73	SIGNAL	76	SIGNAL
74	SIGNAL GROUND	75	SIGNAL GROUND

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

MATERIAL

-

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±0.15

1 PLC ±0.15

2 PLC ±0.15

3 PLC ±

4 PLC ±

ANGLES ±

FINISH -

-

DWN 22MAR2018

CHK TIM XUE 22MAR2018

APVD SEAN HAN 22MAR2018

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

NAME

RECEPTACLE CONNECTOR, VERTICAL, 148 POSITION, SLIVER

SIZE

A2

CAGE CODE

-

DRAWING NO

©2332538

RESTRICTED TO

-

SCALE

4:1

SHEET

3

OF

3

REV

3

TE Connectivity

RECEPTACLE CONNECTOR, VERTICAL, 148 POSITION, SLIVER

4:1

3

3

3

THIS PRODUCT HAS NOT COMPLETED VALIDATION AND QUALIFICATION TESTING

PRELIMINARY NOT RELEASED FOR PRODUCTION

1471-9 (3/13)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2332538-1](#)