


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

CRIMP CONTACT DETAILS

WIRE SIZE	PIN(MALE)	PICTORIAL VIEW
AWG 20	2334110-2	
AWG 22	2334110-3	
AWG 24-28	2334110-4	

CONTACT CRIMP TOOL

PICTORIAL VIEW

601966-1 (COMPACT)
601967-1 (STANDARD)




CONTACT POSTIONER DETAILS (CONTACT TYPE:SOCKET)

CRIMP TOOL	PART NUMBER	PICTORIAL VIEW
COMPACT	601966-2	
STANDARD	1-2823582-4	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±-
1 PLC ±-
2 PLC ±-
3 PLC ±-
4 PLC ±-
ANGLES ±

FINISH

DWN 09APR2018
GOPALAKRISHNA HV
CHK 09APR2018
E STELLINGA
APVD 09APR2018
E STELLINGA

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING



TE Connectivity

NAME
D-SUB CRIMP MALE 9-50 POS

-
-

SIZE

CAGE CODE
A300779

DRAWING NO

C-2334100

RESTRICTED TO

SCALE
4:1

SHEET
2 OF 2

REV
A1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2334100-4](#)