

2018

RELEASED FOR PUBLICATION

THIS DRAWING IS UNPUBLISHED.

BY Tyco Electronics AMP GmbH
© COPYRIGHT 2018

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	11JUL2018	GK	ES

NOTES:

1 COPPER ALLOY.

2 GOLD PLATED OVER NICKEL

3. DURABILITY: 250 MATING CYCLES

4. MAX CURRENT 7A
MAX CONTACT RESISTANCE 10MΩ

NOT IN PRODUCTION

0.24	0.64	24-28	2334108-4
0.23	0.90	22-24	2334108-3
0.22	1.12	20-24	2334108-2
0.23	1.36	18	2334108-1
WEIGHT (g)	D	AWG	PART NO

DIMENSIONS: mm		DWN GOPALAKRISHNA HV 20APR2018		MATERIAL 1		FINISH 2	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		CHK E STELLINGA 20APR2018		 TE Connectivity			
		APVD E STELLINGA 20APR2018					
		PRODUCT SPEC -		NAME SOCKET CRIMP CONTACT AWG 18-28			
		APPLICATION SPEC -		SIZE A 4		CAGE CODE 00779	
WEIGHT SEE TABLE		RESTRICTED TO -		SCALE 6:1		SHEET 1 OF 1	
CUSTOMER DRAWING				REV A			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2334108-2](#)