



	32	1500 +50/-0	4-2336313-3
	32	1000 +50/-0	4-2336313-2
	32	500 +50/-0	4-2336313-1
	32	2000 +80/-0	2336313-4
	32	1500 +50/-0	2336313-3
	32	1000 +50/-0	2336313-2
	32	500 +50/-0	2336313-1
STANDARD	GAGE	" L " mm	PART NO

4805 (3/13)

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



WIRING PATTERN

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN	M. YI	03MAY2018	 TE Connectivity				
			CHK	G. FRANKLIN	03MAY2018					
DIMENSIONS: mm 			TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±.01 1 PLC ±.02 2 PLC ±.03 3 PLC ±.04 4 PLC ±.05 ANGLES ±.01 FINISH			APVD	G. FRANKLIN	03MAY2018	NAME CABLE ASSEMBLY, DIRECT ATTACH QSFP 25GIG , 32 AWG	RESTRICTED TO
						PRODUCT SPEC				
						APPLICATION SPEC				
						WEIGHT				
MATERIAL	-	-	RESTRICTED CUSTOMER			SIZE	CAGE CODE	DRAWING NO		
	-	-				A1	00779	C=2336313		
						SCALE	1:3	SHEET	2	OF 2
								REV	C	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2336313-3](#)