


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	13DEC2018	FL	HL

D


C


B

A



- NOTES:
- 1 MATERIAL CONTACTS; PHOSPHORBRONZE
MATERIAL SHIELD ; PHOSPHORBRONZE
MATERIAL HOUSING; GLASSFILLED POLYESTER (GRAY)
 - 2 GENERAL PLATING SPECIFICATION: UNDERPLATING (ENTIRE CONTACT):
1,27µm NICKEL MIN. AND ACTION PIN: 0,5µm TIN MIN.
FOR PLATING OF MATING SURFACES SEE APPLICABLE
SPECIFICATION REFERENCE FOR EACH DASH NUMBER.
 - 3 CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101 PERFORMANCE LEVEL 2.
 - 4 ASSEMBLY PRINTED WITH P/N AND DATECODE
THE MARKING CAN APPEAR ON THE FRONT SIDE OR BACK SIDE.
 - 5 HOLE PATTERN FOR FEMALE CONNECTOR
PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID
 - 6 ROW "f" 4 PLATED THROUGH HOLES FOR UPPERSHIELD
 - 7 SHIELD MOUNTED ON CONNECTOR WITH DOUBLE SIDED
ADHESIVE TAPE OR ADHESIVE



			<div>23</div>		<div>1</div>		2336682-1	
			FINISH		MATERIAL		PART NUMBER	
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN 17MAY2018 FRED LIU		<div><div>TE</div>TE Connectivity</div>			
			CHK 17MAY2018 ALEX SHOAL					
DIMENSIONS: mm			APVD 17MAY2018 HOPE LIU		NAME Z-PACK 2mm HM 8 COLUMNS PRE-SHIELDED RECEPTACLE			
			TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-60123			
			0 PLC ±- 1 PLC ±0.2 2 PLC ±0.2 3 PLC ±0.2 4 PLC ±- ANGLES ±- FINISH		APPLICATION SPEC 114-19029			
MATERIAL			WEIGHT		SIZE		RESTRICTED TO	
- - -			-		A2		00779	
			CUSTOMER DRAWING		C=2336682		SCALE 4:1	
							SHEET 1 of 1	
							REV A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2336682-1](#)