




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

PACKAGE 2	108-60121	30u"	45.0	10	44.5	91	70	73.15	89	71.65	164	7-2337939-4
PACKAGE 1		30u"	86.5	7.0	44.5	91	70	73.15	89	71.65	164	5-2337939-8
PACKAGE 4		30u"	53.5	7.0	28	58	37	40.15	56	38.65	98	5-2337939-7
PACKAGE 3		30u"	36.5	7.0	19.5	41	20	23.15	39	21.65	64	5-2337939-6
NA		30u"	22.5	7.0	12.5	27	6	9.15	25	7.65	36	5-2337939-5
PACKAGE 1		30u"	10.0	10.0	44.5	91	70	73.15	89	71.65	164	5-2337939-4
PACKAGE 4		30u"	10.0	10.0	28	58	37	40.15	56	38.65	98	5-2337939-3
PACKAGE 3		30u"	10.0	10.0	19.5	41	20	23.15	39	21.65	64	5-2337939-2
NA		30u"	10.0	10.0	12.5	27	6	9.15	25	7.65	36	5-2337939-1
PACKAGE 1		15u"	86.5	7.0	44.5	91	70	73.15	89	71.65	164	4-2337939-8
PACKAGE 4	108-60121-1	15u"	53.5	7.0	28	58	37	40.15	56	38.65	98	4-2337939-7
PACKAGE 3		15u"	36.5	7.0	19.5	41	20	23.15	39	21.65	64	4-2337939-6
NA		15u"	22.5	7.0	12.5	27	6	9.15	25	7.65	36	4-2337939-5
PACKAGE 1		15u"	10.0	10.0	44.5	91	70	73.15	89	71.65	164	4-2337939-4
PACKAGE 4		15u"	10.0	10.0	28	58	37	40.15	56	38.65	98	4-2337939-3
PACKAGE 3		15u"	10.0	10.0	19.5	41	20	23.15	39	21.65	64	4-2337939-2
NA		15u"	10.0	10.0	12.5	27	6	9.15	25	7.65	36	4-2337939-1
PACKAGE 1		G/F	86.5	7.0	44.5	91	70	73.15	89	71.65	164	3-2337939-8
PACKAGE 4		G/F	53.5	7.0	28	58	37	40.15	56	38.65	98	3-2337939-7
PACKAGE 3		G/F	36.5	7.0	19.5	41	20	23.15	39	21.65	64	3-2337939-6
NA		G/F	22.5	7.0	12.5	27	6	9.15	25	7.65	36	3-2337939-5
PACKAGE 1		G/F	10.0	10.0	44.5	91	70	73.15	89	71.65	164	3-2337939-4
PACKAGE 4		G/F	10.0	10.0	28	58	37	40.15	56	38.65	98	3-2337939-3
PACKAGE 3		G/F	10.0	10.0	19.5	41	20	23.15	39	21.65	64	3-2337939-2
NA		G/F	10.0	10.0	12.5	27	6	9.15	25	7.65	36	3-2337939-1
PACKAGE 2	108-60121	30u"	NA		44.5	91	70	73.15	89	71.65	164	2-2337939-5
PACKAGE 1		30u"	NA		44.5	91	70	73.15	89	71.65	164	2-2337939-4
PACKAGE 4		30u"	NA		28	58	37	40.15	56	38.65	98	2-2337939-3
PACKAGE 3		30u"	NA		19.5	41	20	23.15	39	21.65	64	2-2337939-2
NA		30u"	NA		12.5	27	6	9.15	25	7.65	36	2-2337939-1
PACKAGE 1	108-60121-1	15u"	NA		44.5	91	70	73.15	89	71.65	164	6-2337939-4
PACKAGE 4		15u"	NA		28	58	37	40.15	56	38.65	98	6-2337939-3
PACKAGE 3		15u"	NA		19.5	41	20	23.15	39	21.65	64	6-2337939-2
NA		15u"	NA		12.5	27	6	9.15	25	7.65	36	6-2337939-1
PACKAGE 1		G/F	NA		44.5	91	70	73.15	89	71.65	164	2337939-4
PACKAGE 4		G/F	NA		28	58	37	40.15	56	38.65	98	2337939-3
PACKAGE 3		G/F	NA		19.5	41	20	23.15	39	21.65	64	2337939-2
NA		G/F	NA		12.5	27	6	9.15	25	7.65	36	2337939-1
PACKING SPEC	PRODUCT SPEC	GOLD PLATING	W	V	J	D	N	C	B	A	POS.	PART NUMBER
				MYLAR SIZE (PAGE 4)								

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
-
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±0.3

2 PLC ±0.20

3 PLC ±0.050

4 PLC ±-

ANGLES ±-

FINISH -
-

DWN
FRED LIU
CHK
HOPE LU
APVD
HOPE LU

12JUN2018
12JUN2018
12JUN2018

PRODUCT SPEC
-
APPLICATION SPEC
-
WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
PCI EXPRESS CARD EDGE CONNECTOR
GEN4 , STANDARD VERSION

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-2337939

RESTRICTED TO
-




SCALE
3:1

SHEET
2

OF
6

REV
E

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



ADD-IN CARD EDGE-FINGER DIMENSION

164	92.00	70	73.15	72.15	A1,B17,B31,B48,B81
98	59.00	37	40.15	39.15	A1,B17,B31,B48
64	42.00	20	23.15	22.15	A1,B17,B31
36	28.00	6	9.15	8.15	A1,B17
POS.	DIM. E	DIM. F	DIM. G	DIM. H	"K"

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±0.3

1 PLC ±0.20

2 PLC ±0.20

3 PLC ±0.050

4 PLC ±0.050

ANGLES ±

FINISH ±

MATERIAL

-

-

DWN: FRED LIU 12JUN2018

CHK: HOPE LU 12JUN2018

APVD: HOPE LU 12JUN2018

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE Connectivity


NAME: PCI EXPRESS CARD EDGE CONNECTOR GEN4 , STANDARD VERSION

SIZE: A200779 CAGE CODE: C-2337939

DRAWING NO: C-2337939

RESTRICTED TO: -

SCALE: 3:1 SHEET: 3 OF 6 REV: E



D

D

C


C

B



B

A

A



PACKAGE 1



PACKAGE 2

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
FRED LIU
12JUN2018

CHK
HOPE LU
12JUN2018

APVD
HOPE LU
12JUN2018

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±0.3
2 PLC ±0.20
3 PLC ±0.050
4 PLC ±
ANGLES ±
FINISH

MATERIAL

-

-

PRODUCT SPEC
-
APPLICATION SPEC
-
WEIGHT
-

CUSTOMER DRAWING

SCALE 3:1

SHEET 5 OF 6

REV E

TE Connectivity

NAME
PCI EXPRESS CARD EDGE CONNECTOR
GEN4 , STANDARD VERSION

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-2337939

RESTRICTED TO
-

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

D

D

C


C

B


B

A

A



PACKAGE 3



PACKAGE 4

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
FRED LIU
CHK
HOPE LU
APVD
HOPE LU

12JUN2018
12JUN2018
12JUN2018

TE Connectivity

PCI EXPRESS CARD EDGE CONNECTOR
GEN4 , STANDARD VERSION

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±0.3
2 PLC ±0.20
3 PLC ±0.050
4 PLC ±-
ANGLES ±-
FINISH

MATERIAL
-
-

PRODUCT SPEC
-
APPLICATION SPEC
-
WEIGHT
-

CUSTOMER DRAWING

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-2337939

RESTRICTED TO
-

SCALE
3:1

SHEET
6 OF 6

REV
E

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[4-2337939-2](#)