



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	ECO-18-002821	26FEB2018	KH	NN



Dimensions in mm [inches for reference]

Part No.	To Fit Connector Size	H		J		K		P REF b	R REF b	S REF b	U		W ±20% b	X ±20% b
		MIN a	MAX b	MIN a	MAX b	MIN a	MAX b				MIN a	±20% b		
234A111-XXC-0	9 WAY	20.0 [.79]	20.3 [.80]	16.0 [.63]	10.7 [.42]	11.5 [.45]	4.0 [.16]	28.0 [1.10]	19.0 [.75]	13.0 [.51]	1.0 [.04]	3.6 [.14]	1.0 [.04]	3.0 [.12]
234A121-XXC-0	15 WAY	29.0 [1.14]	28.2 [1.11]	15.7 [.62]	10.7 [.42]	11.5 [.45]	5.3 [.21]	35.1 [1.38]	18.8 [.74]	12.7 [.50]	3.0 [.12]	5.0 [.19]	1.0 [.04]	3.0 [.12]
234A132-XXC-0	25 WAY	43.5 [1.71]	42.2 [1.66]	15.0 [.59]	10.7 [.42]	16.0 [.63]	6.4 [.25]	48.0 [1.89]	20.0 [.79]	14.0 [.55]	4.5 [.18]	7.5 [.30]	1.0 [.04]	3.0 [.12]
234A142-XXC-0	37 WAY	60.5 [2.38]	58.7 [2.31]	15.0 [.59]	10.7 [.42]	16.0 [.63]	7.9 [.31]	60.0 [2.36]	20.0 [.79]	14.0 [.55]	3.5 [.14]	5.5 [.22]	1.0 [.04]	3.0 [.12]
234A153-XXC-0	50 WAY	58.1 [2.29]	57.9 [2.28]	16.0 [.63]	13.7 [.54]	24.1 [.95]	14.0 [.55]	63.2 [2.49]	26.4 [1.04]	17.5 [.69]	7.0 [.28]	9.9 [.39]	1.0 [.04]	3.0 [.12]

DIMENSIONS:

mm [INCHES]

DWN

P. VU

05JUL2017

MATERIAL

-

FINISH

-

CHK

N. NAGAR

05JUL2017

APVD

A. POOLE

05JUL2017

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

0

NAME

RIGHT ANGLED BOOT, RECTANGULAR D-SUBMINIATURE, COATED

234A1XX-XXC-0

SIZE

A4

CAGE CODE

00779

DRAWING NO

C-234A1XX-XXC-0

RESTRICTED TO

-

CUSTOMER DRAWING

SCALE

DNS

SHEET

1 OF 2

REV A


RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

COPYRIGHT 2017 By TE Connectivity

0 PLC ± -
 1 PLC ± -
 2 PLC ± -
 3 PLC ± -
 4 PLC ± -
 ANGLES ± -



REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

COMPATIBILITY CHART

Material Dash No.	Material Description	SPEC No.	Coating Slash No.
-25C	ELASTOMER/SILVER COMPOSITE	RW-3047	/86, /200

ORDERING INFORMATION

234A1**—**C/**—0



NOTES

- As supplied dimensions are for parts without adhesive, when an adhesive layer is added entry diameters will reduce by 1.5mm Max.

IT IS ESSENTIAL THAT THESE PARTS ARE INSTALLED ON THE CONNECTOR WITH THE APPROPRIATE INSTALLATION CLAMPING TOOL. THIS ENSURES GOOD CONTACT BETWEEN THE BOOT AND CONNECTOR. THE RECOMMENDED CLAMP PART NUMBER IS :- AT-7-031 TIN PLATED CONNECTORS ARE RECOMMENDED.

RELEASED FOR PUBLICATION


ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

COPYRIGHT 2017 By TE Connectivity



DIMENSIONS:		DWN	05JUL2017	MATERIAL	FINISH	
mm [INCHES]		P. VU		-		-
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK	05JUL2017	TE Connectivity		
		N, NAGAR				
		APVD	05JUL2017			
		A. POOLE				
		PRODUCT SPEC		NAME		
-		RIGHT ANGLED BOOT, RECTANGULAR D-SUBMINIATURE, COATED			234A1XX-XXC-0	
APPLICATION SPEC		SIZE			CAGE CODE	DRAWING NO
-		A4			00779	C-234A1XX-XXC-0
WEIGHT		RESTRICTED TO			-	
CUSTOMER DRAWING		SCALE			DNS	SHEET
2		OF			2	REV
A						



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[EM3693-000](#)