



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED FOR PRODUCTION	06AUG2019	RK	PS

- NOTES:
- MATERIALS & FINISH
HOUSING : PA66, UL94 V0, COLOR - GREEN
PUSH BUTTON : PA66, COLOR - ORANGE.
CONTACT : COPPER ALLOY, TIN PLATED
SPRING : STAINLESS STEEL
 - MECHANICAL
WIRE STRIPPING LENGTH : 12-13 mm
 - ELECTRICAL
WIRE RANGE : 12-26 AWG
RATED VOLTAGE : 300V
RATED CURRENT : 16A
INSULATION RESISTANCE : >2000 M Ohm (500V DC)
 - OPERATING TEMPERATURE RANGE : -40°C TO +105°C
-  TOLERANCE NOT CUMULATIVE

80.0	16	1-2350397-6
75.0	15	1-2350397-5
70.0	14	1-2350397-4
65.0	13	1-2350397-3
60.0	12	1-2350397-2
55.0	11	1-2350397-1
50.0	10	1-2350397-0
45.0	9	2350397-9
40.0	8	2350397-8
35.0	7	2350397-7
30.0	6	2350397-6
25.0	5	2350397-5
20.0	4	2350397-4
15.0	3	2350397-3
10.0	2	2350397-2
DIM A	NO. OF POS	PART NUMBER



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 08APR2019 RAGHAVENDRA.K	 TE Connectivity		
DIMENSIONS: mm		CHK 01JUL2019 KARTHIK.JK			
		APVD 02JUL2019 PRASHANTH.S			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC			
0 PLC ±-		-	NAME SPRING FEMALE PLG, GREEN 5.00mm PITCH		
1 PLC ±-		APPLICATION SPEC	-		
2 PLC ±-		-	SIZE CAGE CODE DRAWING NO RESTRICTED TO		
3 PLC ±-		WEIGHT	A3 00779 C-2350397		
4 PLC ±-		-	SCALE 3:1 SHEET 1 OF 1 REV A		
ANGLES ±		CUSTOMER DRAWING			
FINISH					
SEE NOTES					
-					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2350397-4](#)