





OBSOLETE	10.3±3 GRAMS	5.00±0.08 [.197±.003]	#10	BODY: COPPER ASTM-B187 ANNEALED	277147-5
	-	8.33±0.13 [.328±.005]	5/16	TIN PL MIL-T-10727 0.00381[.000150] MIN THK	277147-4
	-	6.73±0.13 [.265±.005]	1/4	INSERT & FUNNEL: BRASS ASTM B36	277147-3
	10.0±3 GRAMS	9.91±0.13 [.390±.005]	3/8	NICKEL PL SAE AMS QQ-N-290A,	277147-2
	11.0±3 GRAMS	5.00±0.08 [.197±.003]	#10	DATED JULY 2000,	277147-1
				0.00254 [.000100] MIN THK	
WEIGHT		'A'	'B'	MATERIAL & FINISH	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 6/23/89 DK SCHRUM CHK 10/16/90 MS FEHER	 Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: MM [INCHES]	TOLERANCES, UNLESS OTHERWISE SPECIFIED:	APVD 10/23/90 AJ KAUFMAN PRODUCT SPEC	NAME	
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	108-11011 APPLICATION SPEC	WIRE TERMINAL, RING TONGUE, SEALED COPALUM, 8.6mm2 [8] ALUMNIUM 4.8mm2 [10] COPPER	
	MATERIAL	FINISH	SIZE A2	GAGE CODE 00779
SEE TABLE	SEE TABLE	WEIGHT SEE TABLE	DRAWING NO C-277147	RESTRICTED TO -
CUSTOMER DRAWING			SCALE 4:1	SHEET 1 OF 1
			REV N	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[277147-1](#)