






OBSOLETE	-	4.34±0.08 [.171±.003]	#8	BODY: COPPER ASTM-B187 ANNEALED TIN PL MIL-T-10727 0.00457[.000150] MIN THK INSERT & FUNNEL: BRASS ASTM B36 NICKEL PL SAE AMS QQ-N-290A, DATED JULY 2000, 0.00254 [.000100] MIN THK	277148-8
	14.8 ±3 GRAMS	6.73±0.13 [.265±.005]	1/4		277148-7
	15.2 ±3 GRAMS	5.00±0.08 [.197±.003]	#10		277148-6
	17.0 ±3 GRAMS	4.34±0.08 [.171±.003]	#8		277148-5
	15.3 ±3 GRAMS	9.91±0.13 [.390±.005]	3/8		277148-4
	16.2 ±3 GRAMS	8.33±0.13 [.328±.005]	5/16		277148-3
	-	6.73±0.13 [.265±.005]	1/4		277148-2
	16.8 ±3 GRAMS	5.00±0.08 [.197±.003]	#10		277148-1
	WEIGHT	'A'	'B'		
	MATERIAL & FINISH				PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 6/23/89 DK SCHRUM	 TE Connectivity				
		CHK 10/16/90 MS FEHER					
DIMENSIONS: MM [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD 10/23/90 AJ KAUFMAN	NAME				
	0 PLC ± -	PRODUCT SPEC	WIRE TERMINAL, RING TONGUE, SEALED COPALUM				
	1 PLC ± -	108-11011	14.6mm2 [6] ALUMINUM				
	2 PLC ± -	APPLICATION SPEC	8.8mm2 [8] COPPER				
	3 PLC ± -	114-2134	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
	4 PLC ± -	WEIGHT	A2	00779	C=277148	-	
	ANGLES ± -	SEE TABLE	CUSTOMER DRAWING				
MATERIAL	FINISH	SCALE 4:1		SHEET 1 of 1	REV P		
SEE TABLE	SEE TABLE						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[277148-3](#)