






OBSOLETE	—	8.33[.328]	5/16	63.75[2.51]	12.45[.49]	10.18[.401]	BODY: COPPER ASTM-B187 ANNEALED TIN PL PER MIL-T-10727 0.00381[.000150] MIN THK	277151-7
	—	13.08[.515]	1/2	69.34[2.73]	16.76[.66]	11.38[.448]		277151-6
	57.0 ⁺⁵ GRAMS	6.73[.265]	1/4					277151-5
OBSOLETE	—	13.08[.515]	1/2	63.75[2.51]	12.45[.49]	10.18[.401]	INSERT & FUNNEL: BRASS ASTM B36 NICKEL PL SAE AMS QQ-N-290A, DATED JULY 2000, 0.00254 [.000100] MIN THK	277151-4
	54.0 ⁺⁵ GRAMS	6.73[.265]	1/4					277151-3
	56.0 ⁺⁵ GRAMS	9.91[.390]	3/8	69.34[2.73]	16.76[.66]	11.38[.448]		277151-2
53.0 ⁺⁵ GRAMS	63.75[2.51]			12.45[.49]	10.18[.401]	277151-1		
WEIGHT		'A'	'B'	'L'	'C'	'H'	MATERIAL & FINISH	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN 6/23/89 DK SCHRUM		 TE Connectivity					
DIMENSIONS: MM [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK 10/16/90 MS FEHER							
		0 PLC ± -		APVD 10/23/90 AJ KAUFMAN		NAME WIRE TERMINAL, RING TONGUE, SEALED COPALUM 55.5mm2 [1/0] ALUMINUM 34.3mm2 [2] COPPER					
		1 PLC ± -		PRODUCT SPEC							
		2 PLC ± -		108-11011							
		3 PLC ± -		APPLICATION SPEC		SIZE CAGE CODE DRAWING NO RESTRICTED TO					
		4 PLC ± -		114-2134							
		ANGLES ± -		114-2134							
MATERIAL		FINISH		WEIGHT		A2 00779 C=277151					
SEE TABLE		SEE TABLE		SEE TABLE		—					
CUSTOMER DRAWING						SCALE 2:1		SHEET 1 OF 1		REV R	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[277151-5](#)