

THIS DRAWING IS UNPUBLISHED. DIFFUSION RESTREINTE. RELEASED FOR PUBLICATION LIBRE A LA DIFFUSION. ALL RIGHTS RESERVED. TOUS DROITS RESERVES.

20

FILES ADMISSIBLES (ACCEPTABLES WIRES)

JAUGE (AWG) SECTION / 7 BRINS (7 STRANDS)	26-24 0.12-0.22mm ²
ISOLANT: Ø MAX / MATIERE (INSUL.: Ø MAX / MAT'L)	Ø 1.2 / PVC

LOC F DIST 7

P	LTR	DESCRIPTION MODIFICATIONS	DATE	DWN DESS.	APVD APP.
	D1	REVISED PER ECO-11-005150	27APR11	RK	HMR

2.54

DIM A

VOIE N°1
(FIRST POSITION)

"C" ± 0.4

17.8 ± 0.2

4

XX

REPERE VOIE N°1
(IDENTIFIER POSITION NUMBER 1)

"B" +0.12
0

5.1⁰_{-0.3}

8.9 MIN

1.8 ± 0.2

3.4⁰_{-0.1}

4.5⁰_{-0.1}

4.5⁰_{-0.1}

XX

ECHELLE 4:1
SCALE

ECHELLE 4:1
SCALE

46.52	43.18	18	1-281783-8	*
38.90	35.56	15	1-281783-5	*
31.28	27.94	12	1-281783-2	*
26.20	22.86	10	1-281783-0	*
21.12	17.78	8	0-281783-8	*
16.04	12.70	6	0-281783-6	*
13.50	10.16	5	0-281783-5	*
10.96	7.62	4	0-281783-4	*
8.42	5.08	3	0-281783-3	*
5.88	2.54	2	0-281783-2	*

C	A, B	Nb DE POS	REFERENCES (PART No)
DIMENSIONS			

1 CES CONNECTEURS SONT PREVUS POUR ETRE ACCOUPLES AVEC LES EMBASES 'HE1402' SIMPLE RANGEE (THESE CONNECTORS ARE DESIGNED TO BE MATED WITH 'HE1402' HEADERS SINGLE ROW)

2 LES REFERENCES SUIVIES D'UN ' * ' SONT LES VERSIONS NORMALISEES SELON LA 'CEI 603-8' (THE PART-No FOLLOWED BY ' * ' ARE COVERED BY THE INTERNATIONAL STANDARD 'IEC603-8')

3 REVETEMENT DES CONTACTS: ETAME (CONTACTS PLATING: TIN)

4 "X.X" EST REMPLACÉ PAR LES DEUX DEUXIEME CHIFFRES DU COUPLE DES JAUGES AWG ("X.X" REPLACED BY THE TWO SECOND DIGIT OF AWG RANGE AS DEFINED IN TABLE)

5 MATIERES - BOITIER: PBT UL94V0 - CONTACTS: BRONZE PHOSPHOREUX. (MATERIAL - HOUSING : PBT UL94V0 - CONTACTS: PHOSPHOR BRONZE)

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED: (SUIV. NB. DE DECIMALES)		DWN/DESSINE 29NOV2000 C. COMBEDOUZON CHK/VERIFIE 29NOV2000 I. CORRIOL APVD/APROUVE 29NOV2000 Y. PETRONIN		NAME TITRE							
mm		0 PLC/DEC: ±	1 PLC/DEC: ±0.3	2 PLC/DEC: ±	3 PLC/DEC: ±	4 PLC/DEC: ±	ANGLES ±°	PRODUCT SPEC 108-15053	APPLICATION SPEC 114-15031	SIZE FORMAT	CAGE CODE	DRAWING NO No PLAN	RESTRICTED TO RESERVE A
MATERIAL/MATIERE		FINISH/FINITION		WEIGHT MASSE APPROX.		CUSTOMER DRAWING /PLAN CLIENT		UNIQUEMENT POUR REFERENCE		SCALE ECHELLE 5:1	SHEET FEUILLE	OF DE	REV D1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[281783-2](#)