






LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	BY	APP'D
		A		FIRST VERSION	23NOV2015	GF	SM



NOTES :

△ MATERIALS AND FINISH:

1. HOUSING: PA66
2. CONTACTS: BRASS, FINISH: TIN OVER NICKEL UNDERPLATE
3. MUST COMPLY WITH DIRECTIVE 2002/95/EC (RoHS)
4. WIRE TYPES AND SIZES ACCEPTED
5. WIRE RANGE: 14AWG~28AWG.
6. STRIP LENGTH: 10mm
7. PACKAGED IN TRAY.
8. CURRENT RATING: 16Amp AC300V.
9. OPERATION TEMPERATURE: -40°C TO +105°C
10. THIS PART NO. IS THE SAME STRUCTURE AS THE SERIES: 2834078
11. THE DATASHEET AND MORE DETAILS PLEASE FOLLOW THE SERIES: 2834078

PCB Layout

④	SPRING
③	COVER
②	CONTACT
①	HOUSING

41.00	8 POSN	284078-7
36.00	7 POSN	284078-6
31.00	6 POSN	284078-5
26.00	5 POSN	284078-4
21.00	4 POSN	284078-3
16.00	3 POSN	284078-2
11.00	2 POSN	284078-1
DIM A	NO. OF POSITIONS	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT				REVISIONS			
DATE	BY	CHK	APP'D	DATE	BY	CHK	APP'D
23NOV2015	SHI LING			23NOV2015			
PRODUCT NAME	PROJECT CODE	DATE	BY	DATE	BY	CHK	APP'D
5.00mm 45° Entry Screwless Connector	108-137146	11-137146	SHI LING	23NOV2015			
VERSION	SIZE	DATE	BY	DATE	BY	CHK	APP'D
-	A200779	C-2834078	SHI LING	23NOV2015			
CUSTOMER DRAWING	SCALE	1:1	1	1	1	1	1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2834078-1](#)