



- NOTES :
- ▲ MATERIALS AND FINISH:
 - HOUSING: PA66
 - CONTACTS: BRASS, FINISH: TIN OVER NICKEL UNDERPLATE
- MUST COMPLY WITH DIRECTIVE 2002/95/EC (ROHS)
 - WIRE TYPES AND SIZES ACCEPTED
 WIRE RANGE: 20AWG~28AWG.
 STRIP LENGTH: 5.5mm~6.5mm
 - PACKAGED IN TRAY.
 - CURRENT RATING: 4Amp AC150V.
 - OPERATION TEMPERATURE: -40°C TO +105°C
 - THIS PART NO. IS THE SAME STRUCTURE AS THE SERIES: 2834084
 - THE DATASHEET AND MORE DETAILS PLEASE FOLLOW THE SERIES: 2834084

④	WIRE PROTECTOR
③	CONTACT
②	COVER
①	HOUSING
21.50	8 POSN 2834084-7
19.00	7 POSN 2834084-6
16.50	6 POSN 2834084-5
14.00	5 POSN 2834084-4
11.50	4 POSN 2834084-3
9.00	3 POSN 2834084-2
6.50	2 POSN 2834084-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

STI TE Connectivity

NAME: 2.5 45Entry Screwless Connector

DATE: 08DEC2015

REV: A

SIZE: A2 00779

SCALE: 1:1

SHEET: 1 OF 1

REV: A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2834084-4](#)