


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	PRODUCTION RELEASE	30AUG2019	SS	PS
	A1	REMOVED TOLERANCE FROM DIM F	18DEC2019	AY	PS

NOTES:


- MATERIAL
HOUSING & P&P CAP : HIGH TEMPERATURE THERMOPLASTIC, UL94-V0;COLOR-BLACK
CONTACT PIN : COPPER ALLOY
FINISH :
MATING SIDE : MIN. 0.1 µm GOLD OVER NICKEL UNDER PLATING.
SOLDER SIDE : MIN. 2.0 µm BRIGHT TIN OVER NICKEL UNDER PLATING.
- PACKAGING: TUBE (WITH PICK AND PLACE CAP).
- TOLERANCE NOT CUMULATIVE.
- CUTTING BURR MAX. 0.25 mm.







48.0	50.0	25	2-2842130-5
46.0	48.0	24	2-2842130-4
44.0	46.0	23	2-2842130-3
42.0	44.0	22	2-2842130-2
40.0	42.0	21	2-2842130-1
38.0	40.0	20	2-2842130-0
36.0	38.0	19	1-2842130-9
34.0	36.0	18	1-2842130-8
32.0	34.0	17	1-2842130-7
30.0	32.0	16	1-2842130-6
28.0	30.0	15	1-2842130-5
26.0	28.0	14	1-2842130-4
24.0	26.0	13	1-2842130-3
22.0	24.0	12	1-2842130-2
20.0	22.0	11	1-2842130-1
18.0	20.0	10	1-2842130-0
16.0	18.0	9	2842130-9
14.0	16.0	8	2842130-8
12.0	14.0	7	2842130-7
10.0	12.0	6	2842130-6
8.0	10.0	5	2842130-5
6.0	8.0	4	2842130-4
DIM "F"	DIM "E"	POS. PER ROW	TE PN


1-2842130-0 AS SHOWN

PICK AND PLACE CAP	3
CONTACT PIN	2
HOUSING	1
DESCRIPTION	ITEM NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 05AUG2019 SUBHASREE S	 TE Connectivity		
		CHK 08AUG2019 KARTHIK JK			
		APVD 09AUG2019 PRASHANTH S			
		PRODUCT SPEC			
DIMENSIONS: mm		108-64040	NAME AMPMODU 2mm BREAKAWAY HEADER, DUAL ROW, VERTICAL, 0.1 Au, TUBE WITH PICK AND PLACE CAP		
		APPLICATION SPEC	SIZE		
		114-32259	A3 00779		
MATERIAL SEE NOTES		WEIGHT -	DRAWING NO C-2842130		
FINISH SEE NOTES		CUSTOMER DRAWING			RESTRICTED TO -
		SCALE 5:1	SHEET 1 OF 1		REV A1



RECOMMENDED PCB HOLE PATTERN FOR THROUGH HOLE WAVE



RECOMMENDED PCB HOLE PATTERN FOR THROUGH HOLE REFLOW /PIN-IN-PASTE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2842130-0](#)