



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	PRODUCTION RELEASE	30AUG2019	SS	PS
	A1	REMOVED TOLERANCE FROM DIM F	18DEC2019	AY	PS
	A2	ADDED POSITION 2 AND 3	11JUN2020	AY	PS

NOTES:

- MATERIAL
HOUSING : HIGH TEMPERATURE THERMOPLASTIC, UL94-V0;COLOR- BLACK
CONTACT PIN : COPPER ALLOY
FINISH :
MATING SIDE : MIN. 0.76 µm GOLD OVER NICKEL UNDER PLATING.
SOLDER SIDE : MIN. 2.0 µm NRIGHT TIN OVER NICKEL UNDER PLATING.
- PACKAGING: TUBE.
- TOLERANCE NOT CUMULATIVE.
- CUTTING BURR MAX. 0.25 mm





48.0	50.0	25	2-2842152-5
46.0	48.0	24	2-2842152-4
44.0	46.0	23	2-2842152-3
42.0	44.0	22	2-2842152-2
40.0	42.0	21	2-2842152-1
38.0	40.0	20	2-2842152-0
36.0	38.0	19	1-2842152-9
34.0	36.0	18	1-2842152-8
32.0	34.0	17	1-2842152-7
30.0	32.0	16	1-2842152-6
28.0	30.0	15	1-2842152-5
26.0	28.0	14	1-2842152-4
24.0	26.0	13	1-2842152-3
22.0	24.0	12	1-2842152-2
20.0	22.0	11	1-2842152-1
18.0	20.0	10	1-2842152-0
16.0	18.0	9	2842152-9
14.0	16.0	8	2842152-8
12.0	14.0	7	2842152-7
10.0	12.0	6	2842152-6
8.0	10.0	5	2842152-5
6.0	8.0	4	2842152-4
4.0	6.0	3	2842152-3
2.0	4.0	2	2842152-2
DIM "F"	DIM "E"	POS. PER ROW	TE PN


1-2842152-0 AS SHOWN

CONTACT PIN	2
HOUSING	1
DESCRIPTION	ITEM NO.
THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm	DWN 08AUG2019 SUBHASREE S
	CHK 13AUG2019 KARTHIK JK
	APVD 14AUG2019 PRASHANTH S
	PRODUCT SPEC 108-64040
MATERIAL SEE NOTES	APPLICATION SPEC 114-32259
	WEIGHT -
CUSTOMER DRAWING	

TE Connectivity		NAME	
AMPMODU 2mm BREAKAWAY HEADER, DUAL ROW, RIGHT ANGLE, 0.76 Au, TUBE		RESTRICTED TO	
SIZE	CAGE CODE	DRAWING NO	
A3	00779	C=2842152	
SCALE		SHEET	REV
5:1		1 OF 1	A2



RECOMMENDED PCB HOLE PATTERN FOR THROUGH HOLE WAVE



RECOMMENDED PCB HOLE PATTERN FOR THROUGH HOLE REFLOW /PIN-IN-PASTE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2842152-6](#)