

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20


© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	C2	REVISED PER ECO-14-015436	13OCT2014	NK	MM



WIRE ENTRY


MATING FACE



1.9
REF




3.81±0.05



POLARIZATION KEY SLOT

CLAMPING SCREW



284507-3 AS SHOWN



MATERIALS AND FINISH

HOUSING: PA 6.6, UL 94-V0, COLOR GREEN

CLAMP: BRASS, NICKEL PLATED

TERMINAL: BRASS, TIN PLATED

CONTACT SPRING: PHOSPHOR BRONZE, TIN PLATED

CLAMPING SCREW: M2, BRASS, NICKEL PLATED

2

END-TO-END STACKABLE WITHOUT LOSS OF
CENTERLINE SPACING

3

WIRE SIZE RANGE
14 - 30 AWG



NOT CUMULATIVE TOLERANCE



HOUSING: PA 6.6, UL 94-V0, COLOR: RED



PRELIMINARY - NOT RELEASED FOR PRODUCTION



19.05	5	3-284507-5
10.5	4	3-284507-4
7.0	3	3-284507-3
95.25	25	2-284507-5
91.44	24	2-284507-4
87.63	23	2-284507-3
83.82	22	2-284507-2
80.01	21	2-284507-1
76.20	20	2-284507-0
72.39	19	1-284507-9
68.58	18	1-284507-8
64.77	17	1-284507-7
60.96	16	1-284507-6
57.15	15	1-284507-5
53.34	14	1-284507-4
49.53	13	1-284507-3
45.72	12	1-284507-2
41.91	11	1-284507-1
38.10	10	1-284507-0
34.29	9	284507-9
30.48	8	284507-8
26.67	7	284507-7
22.86	6	284507-6
19.05	5	284507-5
15.24	4	284507-4
11.43	3	284507-3
7.62	2	284507-2
DIM A	NO OF POS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 05FEB2002

E. ZANOLINI

CHK 05FEB2002

E. ZANOLINI

APVD 05FEB2002

D. BIEVENOUR

PRODUCT SPEC

108-20166

APPLICATION SPEC

114-20079

WEIGHT

-

CUSTOMER DRAWING



TE Connectivity

NAME

TERMINAL BLOCK PLUG
STACKING
3.81mm PITCH

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-284507

-

SCALE

4:1

SHEET

OF

REV

C2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[284507-6](#)