



D




D



NOTES;
1 MATERIAL: HOUSING - 66 NYLON (UL94V-0)
POST - TIN BRASS
2 7-292132-3 WAS OBSOLETE.


C

C



B

B



	7-292132-5	5-292132-5	3-292132-5	1-292132-5	15	28	31.8	25.2	31.0
	7- -4	5- -4	3- -4	1- -4	14	26	29.8	23.2	29.0
	7- -3	5- -3	3- -3	1- -3	13	24	27.8	21.2	27.0
	7- -2	5- -2	3- -2	1- -2	12	22	25.8	19.2	25.0
	7- -1	5- -1	3- -1	1- -1	11	20	23.8	17.2	23.0
	7- -0	5- -0	3- -0	1- -0	10	18	21.8	15.2	21.0
	6- -9	4- -9	2- -9	-9	9	16	19.8	13.2	19.0
	6- -8	4- -8	2- -8	-8	8	14	17.8	11.2	17.0
	6- -7	4- -7	2- -7	-7	7	12	15.8	9.2	15.0
8-292132-6	6- -6	4- -6	2- -6	-6	6	10	13.8	7.2	13.0
	6- -5	4- -5	2- -5	-5	5	8	11.8	5.2	11.0
	6- -4	4- -4	2- -4	-4	4	6	9.8	3.2	9.0
	6- -3	4- -3	2- -3	-3	3	4	7.8	—	7.0
	6-292132-2	4-292132-2	2-292132-2	292132-2	2	2	5.8	—	5.0
RED	BLACK	YELLOW	BLUE	NATURAL	Pos.	A	B	C	D

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION

DIMENSIONS:
mm

MATERIAL
1

TOLERANCES UNLESS OTHERWISE SPECIFIED:
±0.2

0-PLC ±
1-PLC ±
2-PLC ±
3-PLC ±
4-PLC ±
ANGLES ±
FINISH
1

DWN
J. JIANG
23JAN03

CHK
S. YAO
23JAN03

APVD
T. SASAKI
23JAN03

PRODUCT SPEC
108-60016

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

Tyco Electronics Corporation
Shanghai, P.R.China, 200233

NAME

POST HEADER ASS'Y (BOX-V DIP)
(AMP CT CONNECTOR 2mm PITCH)

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-292132

RESTRICTED TO
—

SCALE
5:1

SHEET
1 OF 2

REV
A2

A


A



△ MATERIAL: HOUSING - 66 NYLON (UL94V-0)
POST - TIN BRASS



6~15 Pos.




NOT ACCUMULATED TOLERANCE

RECOMMENDABLE P.C.BOARD LAYOUT

(PCB THK:0.8-1.6)

	7-292132-5	5-292132-5	3-292132-5	1-292132-5	15	28	31.8	25.2	31.0
	7-  -4	5-  -4	3-  -4	1-  -4	14	26	29.8	23.2	29.0
	7-  -3	5-  -3	3-  -3	1-  -3	13	24	27.8	21.2	27.0
	7-  -2	5-  -2	3-  -2	1-  -2	12	22	25.8	19.2	25.0
	7-  -1	5-  -1	3-  -1	1-  -1	11	20	23.8	17.2	23.0
	7-  -0	5-  -0	3-  -0	1-  -0	10	18	21.8	15.2	21.0
	6-  -9	4-  -9	2-  -9	 -9	9	16	19.8	13.2	19.0
	6-  -8	4-  -8	2-  -8	 -8	8	14	17.8	11.2	17.0
	6-  -7	4-  -7	2-  -7	 -7	7	12	15.8	9.2	15.0
8-292132-6	6-  -6	4-  -6	2-  -6	 -6	6	10	13.8	7.2	13.0
	6-  -5	4-  -5	2-  -5	 -5	(SEE SHEET 1 OF 2)				
	6-  -4	4-  -4	2-  -4	 -4					
	6-  -3	4-  -3	2-  -3	 -3					
	6-292132-2	4-292132-2	2-292132-2	292132-2					
RED	BLACK	YELLOW	BLUE	NATURAL	Pos.	A	B	C	D
PART NO.									

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN CHK APVD PRODUCT SPEC APPLICATION SPEC WEIGHT		tyco Electronics Tyco Electronics Corporation Shanghai, P.R.China,200233	
DIMENSIONS: MM 		TOLERANCES UNLESS OTHERWISE SPECIFIED: ± 0.2 0-PLC $\pm$ 1-PLC $\pm$ 2-PLC $\pm$ 3-PLC $\pm$ 4-PLC $\pm$ ANGLES $\pm$		NAME POST HEADER ASS'Y (BOX-V DIP) (AMP CT CONNECTOR 2mm PITCH)	
MATERIAL 		FINISH 		SIZE A3	
				CAGE CODE 00779	
				DRAWING NO C-292132	
				RESTRICTED TO -	
CUSTOMER DRAWING				SCALE 5:1	
				SHEET ? OF ?	
				REV A2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[6-292132-4](#)