

4

3

2

1

THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

© COPYRIGHT 2001 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
		P	LTR	DESCRIPTION	DATE
ES	00		A	REVISED FB00-0217-04	16DEC04


D

D




C

C



B



B



A

A

PANEL CUT DIMENSIONS



NOTES

1. MATERIAL
HOUSING: THERMO PLASTIC (BLACK)
CONTACT: COPPER ALLOY
2. CONTACT FINISH
MATING SIDE: NICKEL PL.
ALL OVER GOLD PL.
CT MATING SIDE: NICKEL PL.
ALL OVER MATTE TIN PL.
3. APPLIED AC CONTACT P/N
4. AC: POWER CONTACT (UNLOADED)
DC: SIGNAL CONTACT (PRELOADED)
5. CORE-OUT ARE AT RANDOM.

FINISH	AWG	P/N
TIN PL.	#16~20	1-179321-2
Au PL.	#16~20	179321-3

MT TYPE: 173977-7 CLIMPII TYPE: 179228-7	1-292192-3	1.2 ±0.08	10	15 MAX	46.3	3.3	44.3	51.5	16.4	12	14	6	2	DC7 AC3	2-292189-3
APPLIED CT CONN P/N	MATING COUNTER P/N	APPLIED PANEL THICKNESS H	K	J	G	F	E	D	C	B	A	n	N	POS	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: MM	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0-PLC ± ±0.3
	1-PLC ± ±3°
	2-PLC ± ±3°
	3-PLC ± ±3°
	4-PLC ± ±3°
	ANGLES ±
MATERIAL	FINISH

DWN J.JIANG	05FEB03
CHK S.YAO	05FEB03
APVD T.SASAKI	05FEB03
PRODUCT SPEC	108-60023
APPLICATION SPEC	
WEIGHT	
CUSTOMER DRAWING	

tyco
Electronics

Tyco Electronics Corporation
Shanghai, P.R.China, 200233

NAME
HYBRID SF DRAWER CONN.
PLUG ASSEMBLY

SIZE A3	CAGE CODE 00779	DRAWING NO C-292189	RESTRICTED TO —
------------	--------------------	------------------------	--------------------

SCALE 2:1 SHEET 1 OF 1 REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-292189-3](#)