

NOTES:  
1.MATERIAL:  
HOUSING:NYLON(G.F.) UL94V-0,COLOR:GRAY,BLUE, BLACK  
POST: PRE-TIN 0.5mm SQ. BRASS WIRE


TOLERANCES UNLESS  
OTHERWISE SPECIFIED:

$10 \geq * : \pm 0.2$   
 $30 \geq * > 10 : \pm 0.25$   
 $100 \geq * > 30 : \pm 0.3$   
 ANGLE :  $\pm 3^\circ$

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mr



	MATERIAL
--	----------

SEE NOTE 1

TOLERANCES UNLESS  
OTHERWISE SPECIFIED:

0	PLC
1	PLC
2	PLC
3	PLC
4	PLC
ANGLES	

ANGLES
FINISH

$\pm -$   
 $\pm -$   
 $\pm -$   
 $\pm -$   
 $\pm -$   
 $\pm -$

SEE NOTE 1

[illegible]

3	NAME	AMP Mini CT Connector 1.5mm Pitch Single Row Post HDR Ass'y (V) DIP Staggered Type with Boss with Kink
---	------	--

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
------	-----------	------------	---------------

SIZE	SIZE CODE	DRAWING NO.
A3	00779	C-292207

SCALE	SHEET	REV
-------	-------	-----

SHEET		REV
-------	--	-----

		REV

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION  
- , - .

© COPYRIGHT - By -

ALL RIGHTS RESERVED.


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

0.96	32.5	30.6	28.5	20	7-292207-0	4-292207-0	2-292207-0
0.91	31.0	29.1	27.0	19	6-292207-9	3-292207-9	1-292207-9
0.87	29.5	27.6	25.5	18	6-292207-8	3-292207-8	1-292207-8
0.82	28.0	26.1	24.0	17	6-292207-7	3-292207-7	1-292207-7
0.78	26.5	24.6	22.5	16	6-292207-6	3-292207-6	1-292207-6
0.73	25.0	23.1	21.0	15	6-292207-5	3-292207-5	1-292207-5
0.69	23.5	21.6	19.5	14	6-292207-4	3-292207-4	1-292207-4
0.64	22.0	20.1	18.0	13	6-292207-3	3-292207-3	1-292207-3
0.60	20.5	18.6	16.5	12	6-292207-2	3-292207-2	1-292207-2
0.55	19.0	17.1	15.0	11	6-292207-1	3-292207-1	1-292207-1
0.51	17.5	15.6	13.5	10	6-292207-0	3-292207-0	1-292207-0
0.46	16.0	14.1	12.0	9	5-292207-9	2-292207-9	292207-9
0.42	14.5	12.6	10.5	8	5-292207-8	2-292207-8	292207-8
0.37	13.0	11.1	9.0	7	5-292207-7	2-292207-7	292207-7
0.33	11.5	9.6	7.5	6	5-292207-6	2-292207-6	292207-6
0.28	10.0	8.1	6.0	5	5-292207-5	2-292207-5	292207-5
0.24	8.5	6.6	4.5	4	5-292207-4	2-292207-4	292207-4
0.19	7.0	5.1	3.0	3	5-292207-3	2-292207-3	292207-3
0.16	5.5	3.6	1.5	2	5-292207-2	2-292207-2	292207-2
WEIGHT (g)	C	B	A	Pos.	BLUE	BLACK	GRAY
	DIMENSIONS				P/N		

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -  
1 PLC ± -  
2 PLC ± -  
3 PLC ± -  
4 PLC ± -  
ANGLES ± -  
FINISH

SEE NOTE 1

MATERIAL

SEE NOTE 1

DWN  
S.YAO  
31JAN03

CHK  
S.YAO  
31JAN03


APVD  
T. SASAKI  
31JAN03

PRODUCT SPEC  
108 - 60018

APPLICATION SPEC  
114 - 5223

WEIGHT  
0.000000

CUSTOMER DRAWING

TE Connectivity

NAME  
AMP Mini CT Connector 1.5mm Pitch  
Single Row Post HDR Ass'y (V)  
DIP Staggered Type with Boss with Kink

SIZE  
A3

CAGE CODE  
00779

DRAWING NO  
C-292207

RESTRICTED TO  
-

SCALE  
-

SHEET  
2 OF 2

REV  
B

1470-19 (1/15)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3-292207-0](#)