










REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	ECR-18-017107	07NOV18	T.Q	W.H



NOTES:
1.MATERIAL:
HOUSING:NYLON(G.F.) UL94V-0,COLOR:GRAY,BLUE, BLACK
POST: PRE-TIN 0.5mm SQ. BRASS WIRE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

10 ≥ *	: ±0.2
30 ≥ * > 10	: ±0.25
100 ≥ * > 30	: ±0.3
ANGLE	: ±3°

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.YAO	31JAN03	TE Connectivity	
		CHK S.YAO	31JAN03		
DIMENSIONS: mm		APVD T. SASAKI	31JAN03	NAME AMP Mini CT Connector 1.5mm Pitch Single Row Post HDR Ass'y (V) DIP Staggered Type with Boss with Kink	
		PRODUCT SPEC 108 - 60018		SIZE	RESTRICTED TO
		APPLICATION SPEC 114 - 5223		CAGE CODE	
MATERIAL SEE NOTE 1		WEIGHT 0.000000		DRAWING NO A300779C-292207	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH		CUSTOMER DRAWING		SCALE —	SHEET 1 of 2
SEE NOTE 1		SEE NOTE 1		REV B	

4

3

2


1

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

0.96	32.5	30.6	28.5	20	7-292207-0	4-292207-0	2-292207-0
0.91	31.0	29.1	27.0	19	6-292207-9	3-292207-9	1-292207-9
0.87	29.5	27.6	25.5	18	6-292207-8	3-292207-8	1-292207-8
0.82	28.0	26.1	24.0	17	6-292207-7	3-292207-7	1-292207-7
0.78	26.5	24.6	22.5	16	6-292207-6	3-292207-6	1-292207-6
0.73	25.0	23.1	21.0	15	6-292207-5	3-292207-5	1-292207-5
0.69	23.5	21.6	19.5	14	6-292207-4	3-292207-4	1-292207-4
0.64	22.0	20.1	18.0	13	6-292207-3	3-292207-3	1-292207-3
0.60	20.5	18.6	16.5	12	6-292207-2	3-292207-2	1-292207-2
0.55	19.0	17.1	15.0	11	6-292207-1	3-292207-1	1-292207-1
0.51	17.5	15.6	13.5	10	6-292207-0	3-292207-0	1-292207-0
0.46	16.0	14.1	12.0	9	5-292207-9	2-292207-9	292207-9
0.42	14.5	12.6	10.5	8	5-292207-8	2-292207-8	292207-8
0.37	13.0	11.1	9.0	7	5-292207-7	2-292207-7	292207-7
0.33	11.5	9.6	7.5	6	5-292207-6	2-292207-6	292207-6
0.28	10.0	8.1	6.0	5	5-292207-5	2-292207-5	292207-5
0.24	8.5	6.6	4.5	4	5-292207-4	2-292207-4	292207-4
0.19	7.0	5.1	3.0	3	5-292207-3	2-292207-3	292207-3
0.16	5.5	3.6	1.5	2	5-292207-2	2-292207-2	292207-2
WEIGHT (g)	C	B	A	Pos.	BLUE	BLACK	GRAY
	DIMENSIONS				P/N		

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL
SEE NOTE 1

TOLERANCES UNLESS OTHERWISE SPECIFIED:


0 PLC ± —
1 PLC ± —
2 PLC ± —
3 PLC ± —
4 PLC ± —
ANGLES ± —
FINISH

SEE NOTE 1

DWN
S.YAO
CHK
S.YAO
APVD
T. SASAKI
PRODUCT SPEC
108 - 60018
APPLICATION SPEC
114 - 5223
WEIGHT
0.000000

31JAN03
31JAN03
31JAN03

CUSTOMER DRAWING

TE Connectivity

NAME
AMP Mini CT Connector 1.5mm Pitch
Single Row Post HDR Ass'y (V)
DIP Staggered Type with Boss with Kink

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-292207

RESTRICTED TO
—

SCALE
—

SHEET
2 OF 2

REV
B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-292207-4](#)