

LOC	DIST	REVISIONS					
FB	00	P	LTR	DESCRIPTION	DATE	DWN	APVD

37.5	33.5	52.4	56	35.8	26.2	400	40	BLACK	9-292229-0
37.5	33.5	40.4	44	34.3	20.2	400	38		8-292229-8
37.5	33.5	40.4	44	32.8	20.2	400	36		8-292229-6
29.5	25.5	40.4	44	31.3	20.2	400	34		8-292229-4
29.5	25.5	40.4	44	29.8	20.2	400	32		8-292229-2
29.5	25.5	40.4	44	28.3	20.2	400	30		8-292229-0
29.5	25.5	40.4	44	26.8	20.2	400	28		7-292229-8
21.5	17.5	40.4	44	25.3	20.2	400	26		7-292229-6
21.5	17.5	40.4	44	23.8	20.2	400	24		7-292229-4
21.5	17.5	28.4	32	22.2	14.2	400	22		7-292229-2
W2	W1	D	C	B	A	QTY/ REEL	POS	COLOR	ON TAPE P/N
DIMENSIONS									

37.5	33.5	52.4	56	35.8	26.2	400	40	BEIGE	4-292229-0
37.5	33.5	40.4	44	34.3	20.2	400	38		3-292229-8
37.5	33.5	40.4	44	32.8	20.2	400	36		3-292229-6
29.5	25.5	40.4	44	31.3	20.2	400	34		3-292229-4
29.5	25.5	40.4	44	29.8	20.2	400	32		3-292229-2
29.5	25.5	40.4	44	28.3	20.2	400	30		3-292229-0
29.5	25.5	40.4	44	26.8	20.2	400	28		2-292229-8
21.5	17.5	40.4	44	25.3	20.2	400	26		2-292229-6
21.5	17.5	40.4	44	23.8	20.2	400	24		2-292229-4
21.5	17.5	28.4	32	22.2	14.2	400	22		2-292229-2
W2	W1	D	C	B	A	QTY/ REEL	POS	COLOR	ON TAPE P/N
DIMENSIONS									

THIS DRAWING IS UNPUBLISHED.
RELEASED FOR PUBLICATION

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

DIMENSIONS: mm		DWN	WIRE RANGE		INSULATION DIA	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK	MATERIAL		FINISH	
0 PLC ±-		APVD	 Tyco Electronics Corporation SHANGHAI, CHINA			
1 PLC ±0.1		PRODUCT SPEC				
2 PLC ±0.15		SEE SHEET 1 OF 4	NAME AMP Mini Common Terminated (CT) Connector 1.5mm PITCH			
3 PLC ±0.001		APPLICATION SPEC	DOUBLE ROW POST HDR ASS'Y (V)			
4 PLC ±0.0001		SEE SHEET 1 OF 4	SMT TYPE WITH BOSS, EMBOSS TAPE PACKAGED			
ANGLES ±-		WEIGHT	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
			A4	00779	C-292229	-
CUSTOMER DRAWING			SCALE	NON	SHEET 2 OF 4	REV B1

4

3





2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
ES	00	-	-		-	-	-

D



D

C



C

B

NOTES:
1.MATERIAL:
HOUSING:HIGH HEAT RESISTANT, GLASS FILLED NYLON, UL94V-0, COLOR:BEIGE, BLACK
POST:Sn-100% BRASS WIRE
TO BE MEASURED WITH CONNECTOR PLACED ON HORIZONTAL DATUM SURFACE,
FLOAT OF SOLDER TINE FROM DATUM SURFACE IS 0.1mm MAX.

TOLERANCES UNLESS OTHERWISE SPECIFIED:
10 > : ±0.2
30 > 10 : ±0.25
100 > 30 : ±0.3
ANGLE : ±3°

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	-	Tyco Electronics Corporation Shanghai, P.R. China, 200233	
DIMENSIONS: mm		CHK	-		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	-	NAME AMP Mini Common Terminated (CT) Connector 1.5mm PITCH DBL ROW POST HDR ASS'Y (V) SMT TYPE WITH BOSS	
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC	-		
MATERIAL SEE NOTE 1		APPLICATION SPEC	-	SIZE	CAGE CODE
FINISH SEE NOTE 1		WEIGHT	-	A3	00779
CUSTOMER DRAWING		DRAWING NO C=292229		RESTRICTED TO -	
		SCALE NON		SHEET 3 of 4	REV B1

A

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


ALL INTERNATIONAL RIGHTS RESERVED.

BY TYCO ELECTRONICS CORPORATION.

© COPYRIGHT

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION		DATE	APVD
—	—		—	—		—	—

31.5	35.5	34.1	28.5	40	9-292229-0	4-292229-0
30.0	34.0	22.6	27.0	38	8-292229-8	3-292229-8
28.5	32.5	31.1	25.5	36	8-292229-6	3-292229-6
27.0	31.0	29.6	24.0	34	8-292229-4	3-292229-4
25.5	29.5	28.1	22.5	32	8-292229-2	3-292229-2
24.0	28.0	26.6	21.0	30	8-292229-0	3-292229-0
22.5	26.5	25.1	19.5	28	7-292229-8	2-292229-8
21.0	25.0	23.6	18.0	26	7-292229-6	2-292229-6
19.5	23.5	22.1	16.5	24	7-292229-4	2-292229-4
18.0	22.0	20.6	15.0	22	7-292229-2	2-292229-2
D	C	B	A	Pos.	BLACK	BEIGE
DIMENSIONS					P/N	

DIMENSIONS:		DWN	MATERIAL		FINISH	
mm		CHK	 Tyco Electronics Corporation Shanghai, P.R. China, 200233			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD				
0 PLC ± -		PRODUCT SPEC				
1 PLC ± -		APPLICATION SPEC				
2 PLC ± -		—	NAME AMP Mini Common Terminated (CT) Conn. 1.5mm PITCH			
3 PLC ± -		—	DBL ROW POST HDR ASS'Y (V) SMT TYPE W BOSS			
4 PLC ± -		—	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
ANGLES ± -		WEIGHT	A4	00779	C-292229	—
			CUSTOMER DRAWING			SCALE NON
			SHEET 4 of 4			REV B1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[4-292229-0](#)