


4

3


2

1

LOC	DIST	REVISIONS					
FB	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			B1	REVISED PER ECO-11-005033	2APR11	RK	HMR



TYPE 1







TYPE 2

VACUUM NOZZLE OUTLINE
(FOR REFERENCE)

TOLERANCES UNLESS OTHERWISE SPECIFIED:	
10>	: ±0.2
30> * >10	: ±0.25
100> * >30	: ±0.3
ANGLE	: ±3°

NOTE:
1. PEELING STRENGTH: 0.20-0.69N (20-70gf)
PEELING ANGLE: 165-180°
PEELING SPEED: 300mm/MINUTE.



		DWN S.XU 31JAN03	 TE Connectivity			
		CHK S.YAO 31JAN03				
DIMENSIONS: mm		APVD T.SASAKI 31JAN03	NAME AMP Mini Common Terminated (CT) Connector 1.5mm PITCH			
		PRODUCT SPEC 108-60018	SINGLE ROW POST HDR ASS'Y (V)			
		APPLICATION SPEC 114-5223	SMT TYPE WITH BOSS, EMBOSS TAPE PACKAGED			
		WEIGHT	SIZE A3	CAGE CODE 00779	DRAWING NO C-292230	RESTRICTED TO -
MATERIAL -		FINISH -	CUSTOMER DRAWING			
			SCALE NON	SHEET 1	OF 4	REV B1


THIS DRAWING IS UNPUBLISHED.
ALL RIGHTS RESERVED.

© COPYRIGHT BY

LOC	DIST	REVISIONS									
FB	00	P	LTR	DESCRIPTION					DATE	DWN	APVD
				SEE SHEET 1							

	TYPE 2	49.5	45.5	6.2	40.4	29.9	44	32.9	20.2±0.15	500	20	BLACK	7-292230-0
		49.5	45.5	4.7	40.4	28.4	44	31.4		500	19		6-292230-9
		49.5	45.5	6.2	40.4	26.9	44	29.9		500	18		6-292230-8
		49.5	45.5	4.7	40.4	25.4	44	28.4		500	17		6-292230-7
		49.5	45.5	6.2	40.4	23.9	44	26.9		500	16		6-292230-6
		49.5	45.5	4.7	40.4	22.4	44	25.4		500	15		6-292230-5
		49.5	45.5	6.2	40.4	20.9	44	23.9		500	14		6-292230-4
		49.5	45.5	4.7	40.4	19.4	44	22.4		500	13		6-292230-3
		37.5	33.5	6.2	28.4	17.9	32	20.9	14.2	500	12		6-292230-2
		37.5	33.5	4.7	28.4	16.4	32	19.4	14.2	500	11		6-292230-1
		37.5	33.5	6.2	28.4	14.9	32	17.9	14.2	500	10		6-292230-0
		37.5	33.5	4.7	28.4	13.4	32	16.4	14.2	500	9		5-292230-9
	TYPE 1	29.5	25.5	6.2	-	11.9	24	14.9	11.5	500	8		5-292230-8
		29.5	25.5	4.7	-	10.4	24	13.4	11.5	500	7		5-292230-7
		29.5	25.5	6.2	-	8.9	24	11.9	11.5	500	6		5-292230-6
		29.5	25.5	4.7	-	7.4	24	10.4	11.5	500	5		5-292230-5
		21.5	17.5	6.2	-	5.9	16	8.9	7.5	500	4		5-292230-4
		21.5	17.5	4.7	-	4.4	16	7.4	7.5	500	3		5-292230-3
		21.5	17.5	2.8	-	2.9	16	5.9	7.5	500	2		-
	TAPE TYPE	W2	W1	F	E	D	C	B	A	QTY/REEL	POS	COLOR	ON TAPE P/N
		DIMENSIONS											

	TYPE 2	49.5	45.5	6.2	40.4	29.9	44	32.9	20.2±0.15	500	20	BEIGE	2-292230-0
		49.5	45.5	4.7	40.4	28.4	44	31.4		500	19		1-292230-9
		49.5	45.5	6.2	40.4	26.9	44	29.9		500	18		1-292230-8
		49.5	45.5	4.7	40.4	25.4	44	28.4		500	17		1-292230-7
		49.5	45.5	6.2	40.4	23.9	44	26.9		500	16		1-292230-6
		49.5	45.5	4.7	40.4	22.4	44	25.4		500	15		1-292230-5
		49.5	45.5	6.2	40.4	20.9	44	23.9		500	14		1-292230-4
		49.5	45.5	4.7	40.4	19.4	44	22.4		500	13		1-292230-3
		37.5	33.5	6.2	28.4	17.9	32	20.9	14.2	500	12		1-292230-2
		37.5	33.5	4.7	28.4	16.4	32	19.4	14.2	500	11		1-292230-1
		37.5	33.5	6.2	28.4	14.9	32	17.9	14.2	500	10		1-292230-0
		37.5	33.5	4.7	28.4	13.4	32	16.4	14.2	500	9		292230-9
	TYPE 1	29.5	25.5	6.2	-	11.9	24	14.9	11.5	500	8		292230-8
		29.5	25.5	4.7	-	10.4	24	13.4	11.5	500	7		292230-7
		29.5	25.5	6.2	-	8.9	24	11.9	11.5	500	6		292230-6
		29.5	25.5	4.7	-	7.4	24	10.4	11.5	500	5		292230-5
		21.5	17.5	6.2	-	5.9	16	8.9	7.5	500	4		292230-4
		21.5	17.5	4.7	-	4.4	16	7.4	7.5	500	3		292230-3
		21.5	17.5	2.8	-	2.9	16	5.9	7.5	500	2		-
	TAPE TYPE	W2	W1	F	E	D	C	B	A	QTY/REEL	POS	COLOR	ON TAPE P/N
		DIMENSIONS											




DIMENSIONS: mm		DWN	MATERIAL	FINISH
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK	 TE Connectivity	
0 PLC ±-		APVD		
1 PLC ±0.1		PRODUCT SPEC	NAME AMP Mini Common Terminated (CT) Connector 1.5mm PITCH	
2 PLC ±0.01		SEE SHEET 1 OF 4	SINGLE ROW POST HDR ASS'Y (V)	
3 PLC ±0.001		APPLICATION SPEC	SMT TYPE WITH BOSS, EMBOSS TAPE PACKAGED	
4 PLC ±0.0001		SEE SHEET 1 OF 4	SIZE	RESTRICTED TO
ANGLES ±-		WEIGHT	CAGE CODE	
			DRAWING NO	
CUSTOMER DRAWING			A4 00779	G-292230
			SCALE	REV
			NON	B1
			SHEET 2 OF 4	

THIS DRAWING IS UNPUBLISHED.





RELEASED FOR PUBLICATION

© COPYRIGHT BY ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
FB	00	P	LTR	DESCRIPTION	DATE
				SEE SHEET 1	



CIRCUIT No.1




NOTES:

1. MATERIAL:
HOUSING: GLASS FILLED, HIGH HEAT RESISTANT NYLON, UL94V-0, COLOR: BEIGE OR BLACK
POST: Sn-100% BRASS WIRE
TO BE MEASURED WITH CONNECTOR PLACED ON HORIZONTAL DATUM SURFACE,
FLOAT OF SOLDER TINE FROM DATUM SURFACE IS 0.1mm MAX.

DWN		CHK		APVD		PRODUCT SPEC		APPLICATION SPEC		WEIGHT		CUSTOMER DRAWING		SCALE		SHEET		OF		REV	
SEE NOTE 1		SEE NOTE 1		A3		00779		C-292230		NON		3		4		B1					

LOC	DIST	REVISIONS					
FB	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			-	SEE SHEET 1	-	-	-

0.98	31.5	32.5	30.6	28.5	20	7-292230-0	2-292230-0
0.93	30.0	31.0	29.1	27.0	19	6-292230-9	1-292230-9
0.89	28.5	29.5	27.6	25.5	18	6-292230-8	1-292230-8
0.84	27.0	28.0	26.1	24.0	17	6-292230-7	1-292230-7
0.80	25.5	26.5	24.6	22.5	16	6-292230-6	1-292230-6
0.75	24.0	25.0	23.1	21.0	15	6-292230-5	1-292230-5
0.71	22.5	23.5	21.6	19.5	14	6-292230-4	1-292230-4
0.66	21.0	22.0	20.1	18.0	13	6-292230-3	1-292230-3
0.62	19.5	20.5	18.6	16.5	12	6-292230-2	1-292230-2
0.57	18.0	19.0	17.1	15.0	11	6-292230-1	1-292230-1
0.52	16.5	17.5	15.6	13.5	10	6-292230-0	1-292230-0
0.48	15.0	16.0	14.1	12.0	9	5-292230-9	292230-9
0.43	13.5	14.5	12.6	10.5	8	5-292230-8	292230-8
0.39	12.0	13.0	11.1	9.0	7	5-292230-7	292230-7
0.34	10.5	11.5	9.6	7.5	6	5-292230-6	292230-6
0.30	9.0	10.0	8.1	6.0	5	5-292230-5	292230-5
0.25	7.5	8.5	6.6	4.5	4	5-292230-4	292230-4
0.20	6.0	7.0	5.1	3.0	3	5-292230-3	292230-3
0.17	4.5	5.5	3.6	1.5	2	-	-
WEIGHT (g)	D	C	B	A	Pos.	BLACK	BEIGE (NAT)
	DIMENSIONS					P/N	

DIMENSIONS: mm		DWN CHK APVD PRODUCT SPEC APPLICATION SPEC WEIGHT		MATERIAL SEE SHEET 1		FINISH SEE SHEET 1	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±				 TE Connectivity			
				NAME AMP MINI COMMON TERMINATED (CT) CONNECTOR 1.5 mm PITCH SINGLE ROW POST HDR ASS'Y (V) SMT TYPE WITH BOSS			
				SIZE A4	CAGE CODE 00779	DRAWING NO C-292230	RESTRICTED TO
CUSTOMER DRAWING				SCALE NON	SHEET 4	OF 4	REV B1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[7-292230-0](#)