






LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—		B1	REVISED ECR-07-028230	26NOV07	A,L	S,Y



SECT B-B



SECT A-A





NOTES:


- ① USE WITH: MT REC CONN P/N: X-353293-X
CRIMP HSG P/N: X-353908-X
CRIMP CONT P/N: 353907-1
353918-1(L/P)
- ② USE WITH POWER CONTACT P/N: 1123907-1 (NOT ASSEMBLED WHEN SHIPPED)
- ③ MATERIAL:
HOUSING: GLASS FILLED THERMOPLASTIC, UL94V-0, GRAY
SIGNAL CONTACT: BRASS
- ④ FINISH (SIGNAL CONTACT):
NICKEL UNDERPLATE ALL OVER
LATTICE MATING AREA: GOLD PLATE
MINI CT MATING AREA: MATTE TIN PLATE
- ⑤ LOCATION OF DATE CODE: AABBCD(N)
(AA: YEAR, BB: WEEK, C: DAY OF WEEK, D: DAYTIME, N: NIGHT)

11.3	25.82	3.75	4.25	34.7	33.7	45.7	53.7	C	14(6+8)	4	5-292246-4
11.3	25.82	3.75	4.25	34.7	33.7	45.7	53.7	B	14(6+8)	4	3-292246-4
11.3	25.82	2.05	2.55	34.7	33.7	45.7	53.7	A	14(6+8)	4	1-292246-4
WEIGHT (g)	G	F	E	D	C	B	A	KEY TYPE	SIGNAL	POWER	PART NUMBER


THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN J. JIANG 05FEB03		 Tyco Electronics Corporation Shanghai, PRC 200233					
DIMENSIONS: mm			CHK S.Y 05FEB03							
			APVD T. SASAKI 05FEB03		NAME RECEPTACLE ASSEMBLY FOR AMP 1.5 PITCH MINI CT HYBRID LATTICE CONNECTOR					
			PRODUCT SPEC 108-60028							
			APPLICATION SPEC 114-5256							
			WEIGHT							
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -			SIZE A2			CAGE CODE 00779	DRAWING NO C-292246	RESTRICTED TO -		
MATERIAL SEE NOTE			FINISH SEE NOTE		SCALE NTS				SHEET 1 of 3	REV B1
CUSTOMER DRAWING										



SECT B-B



SECT A-A




NOTES:

- ① USE WITH MT REC CONN P/N: X-353293-X
CRIMP HSG P/N: X-353908-X
CRIMP CONT P/N: 353907-1
353918-1(L/P)
- ② USE WITH POWER CONTACT P/N: 1123907-1 (NOT ASSEMBLED WHEN SHIPPED)
- ③ MATERIAL:
HOUSING: GLASS FILLED THERMOPLASTIC, UL94V-0, GRAY
SIGNAL CONTACT: BRASS
- ④ FINISH (SIGNAL CONTACT):
NICKEL UNDERPLATE ALL OVER
LATTICE MATING AREA: GOLD PLATE
MINI CT MATING AREA: MATTE TIN PLATE
- ⑤ LOCATION OF DATE CODE: AABBCD(N)
(AA: YEAR, BB: WEEK, C: DAY OF WEEK, D: DAYTIME, N: NIGHT)

13.0	31.82	6.75	7.25	40.7	39.7	51.7	59.7	C	22(10+12)	4	6-292246-2
13.0	31.82	6.75	7.25	40.7	39.7	51.7	59.7	B	22(10+12)	4	4-292246-2
13.0	31.82	5.05	5.55	40.7	39.7	51.7	59.7	A	22(10+12)	4	2-292246-2
WEIGHT (g)	G	F	E	D	C	B	A	KEY TYPE	SIGNAL	POWER	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN —	Tyco Electronics Tyco Electronics Corporation Shanghai ,PRC 200233			
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK —	NAME			
	0 PLC ± —	APVD —	PRODUCT SPEC			
	1 PLC ± —	—	APPLICATION SPEC			
	2 PLC ± —	—	WEIGHT			
	3 PLC ± —	—	CUSTOMER DRAWING			
MATERIAL	FINISH	—	SIZE A2	CAGE CODE 00779	DRAWING NO C=292246	RESTRICTED TO —
		SCALE NTS	SHEET 2 of 3	REV B1		

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
—	—	—	—	SEE SHEET 1	—	—



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±	-
1 PLC	±	-
2 PLC	±	-
3 PLC	±	-
4 PLC	±	-
ANGLES	±	-
FINISH		

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

Tyco Electronics Corporation
Shanghai ,PRC 200233

NAME
RECEPTACLE ASSEMBLY
FOR AMP 1.5 PITCH MINI CT
HYBRID LATTICE CONNECTOR

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=292246

RESTRICTED TO
—

SCALE
NTS

SHEET
3 OF 3

REV
B1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-292246-2](#)